

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584717

Luminaire Tested: **HCC8W45D010SL-HM82555927-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584717
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W45D010SL-HM82555927-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3948.4 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584717
CATALOG NUMBER: HCC8W45D010SL-HM82555927-81PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P584717
 CATALOG NUMBER: HCC8W45D010SL-HM82555927-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89			89	
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79			79	
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71			71	
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64			64	
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58			58	
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53	
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49			49	
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45			45	
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42			42	
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39			39	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	92682
5°	91472
10°	88128
15°	84679
20°	82334
25°	79861
30°	71662
35°	46980
40°	25972
45°	21652
50°	19741
55°	18843
60°	17521
65°	15884
70°	14362
75°	12975
80°	11791
85°	11286



TEST NUMBER: P584717
 CATALOG NUMBER: HCC8W45D010SL-HM82555927-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	277.7	7.0
10°-20°	748.3	19.0
20°-30°	1065.0	27.0
30°-40°	788.3	20.0
40°-50°	390.4	9.9
50°-60°	311.6	7.9
60°-70°	216.3	5.5
70°-80°	116.6	3.0
80°-90°	34.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2091.0	53.0
0°-40°	2879.3	72.9
0°-60°	3581.2	90.7
0°-90°	3948.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3948.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3006	
5°	2955	278
15°	2652	748
25°	2347	1065
35°	1248	788
45°	496	390
55°	350	312
65°	218	216
75°	109	117
85°	32	34
90°	0	



TEST NUMBER: P584717
CATALOG NUMBER: HCC8W45D010SL-HM82555927-81PSMDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3005.6
2.5°	2992.3
5°	2955.1
7.5°	2896.7
10°	2814.5
12.5°	2729.5
15°	2652.5
17.5°	2578.1
20°	2509.0
22.5°	2440.1
25°	2347.2
27.5°	2211.7
30°	2012.6
32.5°	1707.3
35°	1248.0
37.5°	852.3
40°	645.2
42.5°	552.2
45°	496.5
47.5°	451.4
50°	411.5
52.5°	377.0
55°	350.5
57.5°	318.6
60°	284.1
62.5°	249.6
65°	217.7
67.5°	185.8
70°	159.3
72.5°	132.8
75°	108.9
77.5°	87.6
80°	66.4
82.5°	47.7
85°	31.9
87.5°	13.3
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)