

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584738

Luminaire Tested: **HCC8W45D010MW-HM82555930-81WDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
 Report Number: P584738
 TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-7)
 Test Lab: COOPER LIGHTING SOLUTIONS
 Issue Date: 10/21/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO COMMERCIAL
 Catalog Number: HCC8W45D010MW-HM82555930-81WDC
 Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, SPECULAR TRIM
 Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
 CYLINDER
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 5312.1 lumens
 Efficiency: N/A
 Efficacy: 120.7 lumens/watt
 Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.05
 Luminous Opening: Circular (Dia: 0.67' x H: 0')
 CIE Type: Direct

Input Watts (W): 44
 Input Voltage (V): NR
 Input Current (A_{in}): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT



TEST NUMBER: P584738
CATALOG NUMBER: HCC8W45D010MW-HM82555930-81WDC

Luminous Intensity Polar Plot





TEST NUMBER: P584738
 CATALOG NUMBER: HCC8W45D010MW-HM82555930-81WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92		
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84		
3	100	93	87	83	98	91	86	82	89	84	81	86	83	79	84	81	78	77		
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	71	70		
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64		
6	83	73	66	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59		
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	63	59	55	54		
8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50		
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46		
10	66	55	49	45	65	55	49	45	54	48	44	53	48	44	52	48	44	43		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	127450
5°	124018
10°	123075
15°	121241
20°	117571
25°	113185
30°	105727
35°	87496
40°	52829
45°	35576
50°	25637
55°	14618
60°	6439
65°	2313
70°	857
75°	381
80°	0
85°	0



TEST NUMBER: P584738
 CATALOG NUMBER: HCC8W45D010MW-HM82555930-81WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	380.6	7.2
10°-20°	1067.3	20.1
20°-30°	1522.5	28.7
30°-40°	1386.5	26.1
40°-50°	654.0	12.3
50°-60°	257.2	4.8
60°-70°	41.0	0.8
70°-80°	2.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2970.5	55.9
0°-40°	4357.0	82.0
0°-60°	5268.2	99.2
0°-90°	5312.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5312.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4133	
5°	4006	381
15°	3798	1067
25°	3327	1523
35°	2324	1386
45°	816	654
55°	272	257
65°	32	41
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P584738
CATALOG NUMBER: HCC8W45D010MW-HM82555930-81WDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	4133.1
2.5°	4079.3
5°	4006.5
7.5°	3965.4
10°	3930.6
12.5°	3873.7
15°	3797.8
17.5°	3702.9
20°	3582.8
22.5°	3456.4
25°	3326.6
27.5°	3168.5
30°	2969.3
32.5°	2700.6
35°	2324.3
37.5°	1796.1
40°	1312.4
42.5°	1008.8
45°	815.8
47.5°	670.4
50°	534.4
52.5°	401.6
55°	271.9
57.5°	170.8
60°	104.4
62.5°	63.2
65°	31.7
67.5°	15.8
70°	9.5
72.5°	3.2
75°	3.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)