

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584756

Luminaire Tested: **HCC8W45D010SL-HM82555935-81WDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584756
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W45D010SL-HM82555935-81WDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5057.7 lumens
Efficiency: N/A
Efficacy: 114.9 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584756
CATALOG NUMBER: HCC8W45D010SL-HM82555935-81WDH

Luminous Intensity Polar Plot





TEST NUMBER: P584756
 CATALOG NUMBER: HCC8W45D010SL-HM82555935-81WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96	95	93	92
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83	80	77	75
4	93	84	78	73	91	83	77	72	81	76	72		79	74	71		77	73	70	68
5	87	78	71	66	86	77	70	66	75	69	65		73	68	64		71	67	64	62
6	82	72	65	60	80	71	64	60	69	64	59		68	63	59		66	62	58	57
7	77	67	60	55	76	66	59	55	64	59	54		63	58	54		62	57	54	52
8	73	62	55	50	71	61	55	50	60	54	50		59	54	50		58	53	49	48
9	69	58	51	46	67	57	51	46	56	50	46		55	50	46		54	49	46	44
10	65	54	47	43	64	53	47	43	53	47	43		52	46	43		51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	115790
5°	113184
10°	109714
15°	107492
20°	106528
25°	104937
30°	99400
35°	82588
40°	48635
45°	32170
50°	25320
55°	18634
60°	12939
65°	7895
70°	3435
75°	1513
80°	1119
85°	0



TEST NUMBER: P584756
 CATALOG NUMBER: HCC8W45D010SL-HM82555935-81WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	344.3	6.8
10°-20°	951.9	18.8
20°-30°	1410.4	27.9
30°-40°	1303.2	25.8
40°-50°	600.9	11.9
50°-60°	316.0	6.2
60°-70°	111.7	2.2
70°-80°	17.5	0.3
80°-90°	1.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2706.6	53.5
0°-40°	4009.8	79.3
0°-60°	4926.8	97.4
0°-90°	5057.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5057.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3755	
5°	3656	344
15°	3367	952
25°	3084	1410
35°	2194	1303
45°	738	601
55°	347	316
65°	108	112
75°	13	18
85°	0	2
90°	0	



TEST NUMBER: P584756
CATALOG NUMBER: HCC8W45D010SL-HM82555935-81WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3755.0
2.5°	3723.2
5°	3656.5
7.5°	3583.4
10°	3503.9
12.5°	3427.5
15°	3367.1
17.5°	3313.1
20°	3246.3
22.5°	3173.2
25°	3084.2
27.5°	2963.3
30°	2791.6
32.5°	2546.8
35°	2193.9
37.5°	1685.1
40°	1208.2
42.5°	906.1
45°	737.7
47.5°	626.4
50°	527.8
52.5°	432.4
55°	346.6
57.5°	273.4
60°	209.8
62.5°	158.9
65°	108.2
67.5°	63.6
70°	38.1
72.5°	22.3
75°	12.7
77.5°	9.5
80°	6.3
82.5°	3.2
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)