

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584751

Luminaire Tested: **HCC8S45D010MW-HM82555935-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584751
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S45D010MW-HM82555935-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4727.1 lumens
Efficiency: N/A
Efficacy: 107.4 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584751
CATALOG NUMBER: HCC8S45D010MW-HM82555935-81PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P584751
 CATALOG NUMBER: HCC8S45D010MW-HM82555935-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89			89	
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79			79	
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71			71	
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64			64	
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58			58	
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53	
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49			49	
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45			45	
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42			42	
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39			39	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	110961
5°	109516
10°	105509
15°	101381
20°	98574
25°	95608
30°	85798
35°	56244
40°	31092
45°	25926
50°	23636
55°	22558
60°	20981
65°	19015
70°	17193
75°	15524
80°	14100
85°	13480



TEST NUMBER: P584751
 CATALOG NUMBER: HCC8S45D010MW-HM82555935-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	332.4	7.0
10°-20°	895.9	19.0
20°-30°	1275.1	27.0
30°-40°	943.7	20.0
40°-50°	467.4	9.9
50°-60°	373.1	7.9
60°-70°	259.0	5.5
70°-80°	139.5	3.0
80°-90°	41.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2503.4	53.0
0°-40°	3447.1	72.9
0°-60°	4287.6	90.7
0°-90°	4727.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4727.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3598	
5°	3538	332
15°	3176	896
25°	2810	1275
35°	1494	944
45°	594	467
55°	420	373
65°	261	259
75°	130	140
85°	38	41
90°	0	



TEST NUMBER: P584751
CATALOG NUMBER: HCC8S45D010MW-HM82555935-81PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3598.4
2.5°	3582.5
5°	3538.0
7.5°	3468.1
10°	3369.6
12.5°	3267.7
15°	3175.7
17.5°	3086.6
20°	3003.9
22.5°	2921.4
25°	2810.0
27.5°	2647.9
30°	2409.6
32.5°	2044.0
35°	1494.1
37.5°	1020.4
40°	772.4
42.5°	661.2
45°	594.5
47.5°	540.4
50°	492.7
52.5°	451.4
55°	419.6
57.5°	381.5
60°	340.2
62.5°	298.8
65°	260.6
67.5°	222.5
70°	190.7
72.5°	158.9
75°	130.3
77.5°	104.9
80°	79.4
82.5°	57.2
85°	38.1
87.5°	15.8
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)