

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584788

Luminaire Tested: **HCC8W50D010MB-HM82555827-81WDBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584788
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W50D010MB-HM82555827-81WDBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5196.2 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584788
CATALOG NUMBER: HCC8W50D010MB-HM82555827-81WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P584788
 CATALOG NUMBER: HCC8W50D010MB-HM82555827-81WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	97356
5°	96549
10°	95276
15°	96363
20°	104061
25°	113797
30°	112418
35°	93252
40°	54886
45°	35860
50°	27795
55°	18467
60°	8992
65°	2780
70°	938
75°	822
80°	622
85°	1238



TEST NUMBER: P584788
 CATALOG NUMBER: HCC8W50D010MB-HM82555827-81WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	295.4	5.7
10°-20°	867.2	16.7
20°-30°	1516.2	29.2
30°-40°	1474.9	28.4
40°-50°	670.7	12.9
50°-60°	311.0	6.0
60°-70°	52.1	1.0
70°-80°	6.4	0.1
80°-90°	2.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2678.8	51.6
0°-40°	4153.6	79.9
0°-60°	5135.4	98.8
0°-90°	5196.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5196.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3157	
5°	3119	295
15°	3018	867
25°	3345	1516
35°	2477	1475
45°	822	671
55°	344	311
65°	38	52
75°	7	6
85°	4	2
90°	0	



TEST NUMBER: P584788
CATALOG NUMBER: HCC8W50D010MB-HM82555827-81WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	3157.2
2.5°	3150.3
5°	3119.1
7.5°	3084.4
10°	3042.8
12.5°	3011.6
15°	3018.5
17.5°	3074.0
20°	3171.1
22.5°	3282.2
25°	3344.6
27.5°	3309.9
30°	3157.2
32.5°	2890.1
35°	2477.2
37.5°	1908.3
40°	1363.5
42.5°	1016.6
45°	822.3
47.5°	693.9
50°	579.4
52.5°	461.4
55°	343.5
57.5°	235.9
60°	145.8
62.5°	79.8
65°	38.1
67.5°	17.3
70°	10.4
72.5°	6.9
75°	6.9
77.5°	3.5
80°	3.5
82.5°	3.5
85°	3.5
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)