

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584784

Luminaire Tested: **HCC8W50D010MW-HM82555827-81NDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584784
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W50D010MW-HM82555827-81NDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4644.6 lumens
Efficiency: N/A
Efficacy: 96.8 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.92
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584784
CATALOG NUMBER: HCC8W50D010MW-HM82555827-81NDW

Luminous Intensity Polar Plot





TEST NUMBER: P584784

CATALOG NUMBER: HCC8W50D010MW-HM82555827-81NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			90
2	105	99	94	90	102	97	92	88	94	90	87	91	87	85	88	85	83	81			81
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73			73
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	72	68	67			67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61			61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			56
7	77	66	59	54	76	66	59	54	64	58	54	63	58	54	62	57	53	52			52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			48
9	69	58	51	47	68	57	51	47	56	51	46	55	50	46	55	50	46	45			45
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	115775
5°	115465
10°	113537
15°	111878
20°	109200
25°	103654
30°	85495
35°	44021
40°	29470
45°	25271
50°	21804
55°	19032
60°	16904
65°	15191
70°	13767
75°	12391
80°	11081
85°	11039



TEST NUMBER: P584784
 CATALOG NUMBER: HCC8W50D010MW-HM82555827-81NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	352.7	7.6
10°-20°	986.0	21.2
20°-30°	1366.2	29.4
30°-40°	820.6	17.7
40°-50°	449.2	9.7
50°-60°	319.1	6.9
60°-70°	207.2	4.5
70°-80°	110.7	2.4
80°-90°	33.0	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2704.9	58.2
0°-40°	3525.4	75.9
0°-60°	4293.7	92.4
0°-90°	4644.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4644.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3754	
5°	3730	353
15°	3504	986
25°	3046	1366
35°	1169	821
45°	580	449
55°	354	319
65°	208	207
75°	104	111
85°	31	33
90°	0	



TEST NUMBER: P584784
CATALOG NUMBER: HCC8W50D010MW-HM82555827-81NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3754.5
2.5°	3747.5
5°	3730.2
7.5°	3688.5
10°	3626.0
12.5°	3567.1
15°	3504.5
17.5°	3424.8
20°	3327.7
22.5°	3209.6
25°	3046.5
27.5°	2789.8
30°	2401.1
32.5°	1759.2
35°	1169.4
37.5°	864.0
40°	732.1
42.5°	648.9
45°	579.5
47.5°	513.5
50°	454.5
52.5°	399.0
55°	354.0
57.5°	312.2
60°	274.1
62.5°	239.4
65°	208.2
67.5°	177.0
70°	152.7
72.5°	125.0
75°	104.0
77.5°	83.2
80°	62.4
82.5°	45.1
85°	31.2
87.5°	13.9
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)