

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584797

Luminaire Tested: **HCC8W50D010MW-HM82555830-81MDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584797  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-5)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W50D010MW-HM82555830-81MDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5003.1 lumens  
Efficiency: N/A  
Efficacy: 104.2 lumens/watt  
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.81  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 48  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584797  
CATALOG NUMBER: HCC8W50D010MW-HM82555830-81MDH

### Luminous Intensity Polar Plot





TEST NUMBER: P584797  
 CATALOG NUMBER: HCC8W50D010MW-HM82555830-81MDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58
9	76	67	61	57	75	66	61	57	65	60	56	64	60	56	63	59	56	55
10	73	63	57	54	72	63	57	53	62	57	53	61	56	53	60	56	53	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	228805
5°	208504
10°	178147
15°	155355
20°	138468
25°	122830
30°	100568
35°	57750
40°	25626
45°	14914
50°	8606
55°	4914
60°	2720
65°	1729
70°	1226
75°	810
80°	604
85°	1203



TEST NUMBER: P584797  
 CATALOG NUMBER: HCC8W50D010MW-HM82555830-81MDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	609.7	12.2
10°-20°	1367.9	27.3
20°-30°	1637.4	32.7
30°-40°	990.6	19.8
40°-50°	277.6	5.5
50°-60°	86.2	1.7
60°-70°	24.6	0.5
70°-80°	6.7	0.1
80°-90°	2.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3615.1	72.3
0°-40°	4605.7	92.1
0°-60°	4969.4	99.3
0°-90°	5003.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5003.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7420	
5°	6736	610
15°	4866	1368
25°	3610	1637
35°	1534	991
45°	342	278
55°	91	86
65°	24	25
75°	7	7
85°	3	2
90°	0	



TEST NUMBER: P584797  
CATALOG NUMBER: HCC8W50D010MW-HM82555830-81MDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7420.0
2.5°	7209.9
5°	6735.9
7.5°	6200.8
10°	5689.4
12.5°	5242.4
15°	4866.4
17.5°	4534.6
20°	4219.6
22.5°	3928.4
25°	3610.1
27.5°	3251.1
30°	2824.4
32.5°	2272.4
35°	1534.1
37.5°	955.0
40°	636.6
42.5°	457.2
45°	342.0
47.5°	250.6
50°	179.4
52.5°	125.3
55°	91.4
57.5°	60.9
60°	44.1
62.5°	30.5
65°	23.7
67.5°	17.0
70°	13.6
72.5°	6.8
75°	6.8
77.5°	3.4
80°	3.4
82.5°	3.4
85°	3.4
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)