

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584809

Luminaire Tested: **HCC8S50D010MB-HM82555830-81WDWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584809
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S50D010MB-HM82555830-81WDWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5579.0 lumens
Efficiency: N/A
Efficacy: 116.2 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584809
CATALOG NUMBER: HCC8S50D010MB-HM82555830-81WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P584809
 CATALOG NUMBER: HCC8S50D010MB-HM82555830-81WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51	49
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	47	43	41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	97976
5°	97307
10°	97052
15°	99597
20°	107825
25°	115600
30°	113016
35°	94107
40°	57813
45°	40033
50°	30554
55°	20032
60°	12538
65°	9391
70°	9467
75°	10890
80°	12040
85°	10791



TEST NUMBER: P584809
 CATALOG NUMBER: HCC8S50D010MB-HM82555830-81WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	298.7	5.4
10°-20°	895.6	16.1
20°-30°	1541.8	27.6
30°-40°	1493.7	26.8
40°-50°	735.7	13.2
50°-60°	347.2	6.2
60°-70°	136.8	2.5
70°-80°	94.3	1.7
80°-90°	35.1	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2736.0	49.0
0°-40°	4229.8	75.8
0°-60°	5312.7	95.2
0°-90°	5579.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5579.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3177	
5°	3144	299
15°	3120	896
25°	3398	1542
35°	2500	1494
45°	918	736
55°	373	347
65°	129	137
75°	91	94
85°	30	35
90°	0	



TEST NUMBER: P584809
CATALOG NUMBER: HCC8S50D010MB-HM82555830-81WDWB

CANDELA DISTRIBUTION (FULL):

0°	
0°	3177.3
2.5°	3167.3
5°	3143.6
7.5°	3119.8
10°	3099.5
12.5°	3096.1
15°	3119.8
17.5°	3190.9
20°	3285.8
22.5°	3370.5
25°	3397.6
27.5°	3336.6
30°	3174.0
32.5°	2906.4
35°	2499.9
37.5°	1941.0
40°	1436.2
42.5°	1114.4
45°	918.0
47.5°	772.4
50°	636.9
52.5°	501.4
55°	372.6
57.5°	271.0
60°	203.3
62.5°	159.2
65°	128.7
67.5°	111.8
70°	105.0
72.5°	98.2
75°	91.4
77.5°	81.2
80°	67.8
82.5°	50.9
85°	30.5
87.5°	13.6
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)