

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584802

Luminaire Tested: **HCC8W50D010SL-HM82555830-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584802
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W50D010SL-HM82555830-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5037.0 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584802
CATALOG NUMBER: HCC8W50D010SL-HM82555830-81PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P584802
 CATALOG NUMBER: HCC8W50D010SL-HM82555830-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89				
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79				
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71				
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64				
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58				
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53				
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49				
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45				
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42				
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	118233
5°	116694
10°	112420
15°	108022
20°	105035
25°	101875
30°	91420
35°	59926
40°	33133
45°	27622
50°	25186
55°	24037
60°	22350
65°	20270
70°	18320
75°	16549
80°	15023
85°	14400



TEST NUMBER: P584802
 CATALOG NUMBER: HCC8W50D010SL-HM82555830-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	354.2	7.0
10°-20°	954.7	19.0
20°-30°	1358.6	27.0
30°-40°	1005.6	20.0
40°-50°	498.1	9.9
50°-60°	397.5	7.9
60°-70°	275.9	5.5
70°-80°	148.7	3.0
80°-90°	43.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2667.5	53.0
0°-40°	3673.0	72.9
0°-60°	4568.6	90.7
0°-90°	5037.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5037.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3834	
5°	3770	354
15°	3384	955
25°	2994	1359
35°	1592	1006
45°	633	498
55°	447	397
65°	278	276
75°	139	149
85°	41	44
90°	0	



TEST NUMBER: P584802
CATALOG NUMBER: HCC8W50D010SL-HM82555830-81PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3834.2
2.5°	3817.3
5°	3769.9
7.5°	3695.3
10°	3590.3
12.5°	3482.0
15°	3383.7
17.5°	3288.9
20°	3200.8
22.5°	3112.8
25°	2994.2
27.5°	2821.5
30°	2567.5
32.5°	2178.0
35°	1591.9
37.5°	1087.3
40°	823.1
42.5°	704.6
45°	633.4
47.5°	575.8
50°	525.0
52.5°	480.9
55°	447.1
57.5°	406.5
60°	362.4
62.5°	318.4
65°	277.8
67.5°	237.1
70°	203.2
72.5°	169.4
75°	138.9
77.5°	111.8
80°	84.6
82.5°	61.0
85°	40.7
87.5°	17.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)