

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584818

Luminaire Tested: **HCC8S50D010BZ-HM82555835-81NDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584818
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S50D010BZ-HM82555835-81NDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4807.8 lumens
Efficiency: N/A
Efficacy: 100.2 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.92
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584818
CATALOG NUMBER: HCC8S50D010BZ-HM82555835-81NDW

Luminous Intensity Polar Plot





TEST NUMBER: P584818

CATALOG NUMBER: HCC8S50D010BZ-HM82555835-81NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90
2	105	99	94	90	102	97	92	88	94	90	87	91	87	85	88	85	83	81
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	72	68	67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	76	66	59	54	64	58	54	63	58	54	62	57	53	52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48
9	69	58	51	47	68	57	51	47	56	51	46	55	50	46	55	50	46	45
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	119839
5°	119517
10°	117527
15°	115808
20°	113032
25°	107298
30°	88500
35°	45565
40°	30508
45°	26157
50°	22571
55°	19698
60°	17497
65°	15731
70°	14245
75°	12844
80°	11472
85°	11463



TEST NUMBER: P584818
 CATALOG NUMBER: HCC8S50D010BZ-HM82555835-81NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	365.1	7.6
10°-20°	1020.6	21.2
20°-30°	1414.2	29.4
30°-40°	849.4	17.7
40°-50°	465.0	9.7
50°-60°	330.3	6.9
60°-70°	214.5	4.5
70°-80°	114.6	2.4
80°-90°	34.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2799.9	58.2
0°-40°	3649.3	75.9
0°-60°	4444.6	92.4
0°-90°	4807.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4807.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3886	
5°	3861	365
15°	3628	1021
25°	3154	1414
35°	1210	849
45°	600	465
55°	366	330
65°	216	214
75°	108	115
85°	32	34
90°	0	



TEST NUMBER: P584818

CATALOG NUMBER: HCC8S50D010BZ-HM82555835-81NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3886.3
2.5°	3879.1
5°	3861.1
7.5°	3818.1
10°	3753.4
12.5°	3692.3
15°	3627.6
17.5°	3545.1
20°	3444.5
22.5°	3322.4
25°	3153.6
27.5°	2887.8
30°	2485.5
32.5°	1821.1
35°	1210.4
37.5°	894.4
40°	757.9
42.5°	671.7
45°	599.8
47.5°	531.5
50°	470.5
52.5°	413.0
55°	366.4
57.5°	323.2
60°	283.7
62.5°	247.8
65°	215.6
67.5°	183.2
70°	158.0
72.5°	129.3
75°	107.8
77.5°	86.2
80°	64.6
82.5°	46.6
85°	32.4
87.5°	14.4
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)