

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584819

Luminaire Tested: **HCC8W50D010SL-HM82555835-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584819
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W50D010SL-HM82555835-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5339.3 lumens
Efficiency: N/A
Efficacy: 111.2 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584819
CATALOG NUMBER: HCC8W50D010SL-HM82555835-81PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P584819
 CATALOG NUMBER: HCC8W50D010SL-HM82555835-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89		
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71		
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64		
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58		
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53		
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49		
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45		
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42		
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125331
5°	123696
10°	119167
15°	114505
20°	111339
25°	107993
30°	96904
35°	63525
40°	35118
45°	29279
50°	26702
55°	25478
60°	23688
65°	21488
70°	19420
75°	17538
80°	15947
85°	15249



TEST NUMBER: P584819
 CATALOG NUMBER: HCC8W50D010SL-HM82555835-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	375.5	7.0
10°-20°	1011.9	19.0
20°-30°	1440.2	27.0
30°-40°	1065.9	20.0
40°-50°	527.9	9.9
50°-60°	421.3	7.9
60°-70°	292.5	5.5
70°-80°	157.6	3.0
80°-90°	46.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2827.6	53.0
0°-40°	3893.5	72.9
0°-60°	4842.7	90.7
0°-90°	5339.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5339.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4064	
5°	3996	375
15°	3587	1012
25°	3174	1440
35°	1688	1066
45°	671	528
55°	474	421
65°	294	293
75°	147	158
85°	43	46
90°	0	



TEST NUMBER: P584819
CATALOG NUMBER: HCC8W50D010SL-HM82555835-81PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4064.4
2.5°	4046.4
5°	3996.1
7.5°	3917.1
10°	3805.8
12.5°	3690.9
15°	3586.8
17.5°	3486.3
20°	3392.9
22.5°	3299.6
25°	3174.0
27.5°	2990.8
30°	2721.5
32.5°	2308.7
35°	1687.5
37.5°	1152.5
40°	872.4
42.5°	746.8
45°	671.4
47.5°	610.3
50°	556.6
52.5°	509.8
55°	473.9
57.5°	430.9
60°	384.1
62.5°	337.5
65°	294.5
67.5°	251.3
70°	215.4
72.5°	179.6
75°	147.2
77.5°	118.5
80°	89.8
82.5°	64.6
85°	43.1
87.5°	18.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)