

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584848

Luminaire Tested: **HCC8S50D010MW-HM82555927-81MDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
 Report Number: P584848
 TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-5)
 Test Lab: COOPER LIGHTING SOLUTIONS
 Issue Date: 10/21/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO COMMERCIAL
 Catalog Number: HCC8S50D010MW-HM82555927-81MDH
 Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, HAZE TRIM
 Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 4131.0 lumens
 Efficiency: N/A
 Efficacy: 86.1 lumens/watt
 Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.81
 Luminous Opening: Circular (Dia: 0.67' x H: 0')
 CIE Type: Direct

Input Watts (W): 48
 Input Voltage (V): NR
 Input Current (A_{in}): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT



TEST NUMBER: P584848
CATALOG NUMBER: HCC8S50D010MW-HM82555927-81MDH

Luminous Intensity Polar Plot





TEST NUMBER: P584848
 CATALOG NUMBER: HCC8S50D010MW-HM82555927-81MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58
9	76	67	61	57	75	66	61	57	65	60	56	64	60	56	63	59	56	55
10	73	63	57	54	72	63	57	53	62	57	53	61	56	53	60	56	53	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	188919
5°	172161
10°	147091
15°	128277
20°	114332
25°	101419
30°	83035
35°	47684
40°	21162
45°	12315
50°	7110
55°	4059
60°	2245
65°	1423
70°	1010
75°	667
80°	497
85°	991



TEST NUMBER: P584848
 CATALOG NUMBER: HCC8S50D010MW-HM82555927-81MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	503.4	12.2
10°-20°	1129.5	27.3
20°-30°	1352.0	32.7
30°-40°	817.9	19.8
40°-50°	229.2	5.5
50°-60°	71.2	1.7
60°-70°	20.3	0.5
70°-80°	5.5	0.1
80°-90°	1.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2984.9	72.3
0°-40°	3802.8	92.1
0°-60°	4103.2	99.3
0°-90°	4131.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4131.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6126	
5°	5562	503
15°	4018	1129
25°	2981	1352
35°	1267	818
45°	282	229
55°	76	71
65°	20	20
75°	6	6
85°	3	2
90°	0	



TEST NUMBER: P584848
CATALOG NUMBER: HCC8S50D010MW-HM82555927-81MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	6126.5
2.5°	5953.1
5°	5561.8
7.5°	5119.9
10°	4697.6
12.5°	4328.6
15°	4018.2
17.5°	3744.2
20°	3484.1
22.5°	3243.6
25°	2980.8
27.5°	2684.4
30°	2332.0
32.5°	1876.2
35°	1266.7
37.5°	788.5
40°	525.7
42.5°	377.5
45°	282.4
47.5°	206.9
50°	148.2
52.5°	103.5
55°	75.5
57.5°	50.4
60°	36.4
62.5°	25.1
65°	19.5
67.5°	14.0
70°	11.2
72.5°	5.6
75°	5.6
77.5°	2.8
80°	2.8
82.5°	2.8
85°	2.8
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)