

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584875

Luminaire Tested: **HCC8W50D010MB-HM82555930-81WDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584875  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W50D010MB-HM82555930-81WDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5298.8 lumens  
Efficiency: N/A  
Efficacy: 110.4 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 48  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584875  
CATALOG NUMBER: HCC8W50D010MB-HM82555930-81WDH

### Luminous Intensity Polar Plot





TEST NUMBER: P584875

CATALOG NUMBER: HCC8W50D010MB-HM82555930-81WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42	41

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	121310
5°	118579
10°	114943
15°	112619
20°	111608
25°	109939
30°	104139
35°	86525
40°	50953
45°	33701
50°	26524
55°	19521
60°	13562
65°	8267
70°	3606
75°	1585
80°	1190
85°	0



TEST NUMBER: P584875  
 CATALOG NUMBER: HCC8W50D010MB-HM82555930-81WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	360.7	6.8
10°-20°	997.3	18.8
20°-30°	1477.6	27.9
30°-40°	1365.4	25.8
40°-50°	629.5	11.9
50°-60°	331.1	6.2
60°-70°	117.0	2.2
70°-80°	18.4	0.3
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2835.6	53.5
0°-40°	4201.0	79.3
0°-60°	5161.6	97.4
0°-90°	5298.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5298.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3934	
5°	3831	361
15°	3528	997
25°	3231	1478
35°	2298	1365
45°	773	630
55°	363	331
65°	113	117
75°	13	18
85°	0	2
90°	0	



TEST NUMBER: P584875  
CATALOG NUMBER: HCC8W50D010MB-HM82555930-81WDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3934.0
2.5°	3900.7
5°	3830.8
7.5°	3754.1
10°	3670.9
12.5°	3590.9
15°	3527.7
17.5°	3471.0
20°	3401.1
22.5°	3324.4
25°	3231.2
27.5°	3104.6
30°	2924.7
32.5°	2668.2
35°	2298.5
37.5°	1765.5
40°	1265.8
42.5°	949.3
45°	772.8
47.5°	656.3
50°	552.9
52.5°	453.0
55°	363.1
57.5°	286.5
60°	219.9
62.5°	166.6
65°	113.3
67.5°	66.6
70°	40.0
72.5°	23.3
75°	13.3
77.5°	9.9
80°	6.7
82.5°	3.3
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)