

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584924

Luminaire Tested: **HCC8S55D010MW-HM82555827-81WDBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584924
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S55D010MW-HM82555827-81WDBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5439.2 lumens
Efficiency: N/A
Efficacy: 104.6 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 52
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584924
CATALOG NUMBER: HCC8S55D010MW-HM82555827-81WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P584924
 CATALOG NUMBER: HCC8S55D010MW-HM82555827-81WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62			
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	101911
5°	101065
10°	99729
15°	100871
20°	108930
25°	119118
30°	117677
35°	97611
40°	57454
45°	37534
50°	29095
55°	19333
60°	9405
65°	2919
70°	983
75°	870
80°	639
85°	1274



TEST NUMBER: P584924
 CATALOG NUMBER: HCC8S55D010MW-HM82555827-81WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	309.2	5.7
10°-20°	907.7	16.7
20°-30°	1587.1	29.2
30°-40°	1543.8	28.4
40°-50°	702.1	12.9
50°-60°	325.5	6.0
60°-70°	54.6	1.0
70°-80°	6.7	0.1
80°-90°	2.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2804.1	51.6
0°-40°	4347.9	79.9
0°-60°	5375.5	98.8
0°-90°	5439.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5439.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3305	
5°	3265	309
15°	3160	908
25°	3501	1587
35°	2593	1544
45°	861	702
55°	360	326
65°	40	55
75°	7	7
85°	4	2
90°	0	



TEST NUMBER: P584924

CATALOG NUMBER: HCC8S55D010MW-HM82555827-81WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	3304.9
2.5°	3297.7
5°	3265.0
7.5°	3228.6
10°	3185.0
12.5°	3152.4
15°	3159.7
17.5°	3217.7
20°	3319.5
22.5°	3435.7
25°	3501.0
27.5°	3464.8
30°	3304.9
32.5°	3025.3
35°	2593.0
37.5°	1997.4
40°	1427.3
42.5°	1064.1
45°	860.7
47.5°	726.4
50°	606.5
52.5°	483.0
55°	359.6
57.5°	246.9
60°	152.5
62.5°	83.6
65°	40.0
67.5°	18.2
70°	10.9
72.5°	7.3
75°	7.3
77.5°	3.6
80°	3.6
82.5°	3.6
85°	3.6
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)