

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584941

Luminaire Tested: **HCC8S55D010MW-HM82555830-81WDBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
 Report Number: P584941
 TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)
 Test Lab: COOPER LIGHTING SOLUTIONS
 Issue Date: 10/21/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO COMMERCIAL
 Catalog Number: HCC8S55D010MW-HM82555830-81WDBB
 Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
 Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 5311.5 lumens
 Efficiency: N/A
 Efficacy: 102.1 lumens/watt
 Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13
 Luminous Opening: Circular (Dia: 0.67' x H: 0')
 CIE Type: Direct

Input Watts (W): 52
 Input Voltage (V): NR
 Input Current (A_{in}): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT



TEST NUMBER: P584941
CATALOG NUMBER: HCC8S55D010MW-HM82555830-81WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P584941
 CATALOG NUMBER: HCC8S55D010MW-HM82555830-81WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	99518
5°	98691
10°	97390
15°	98499
20°	106371
25°	116322
30°	114914
35°	95323
40°	56102
45°	36658
50°	28409
55°	18876
60°	9189
65°	2846
70°	965
75°	846
80°	622
85°	1238



TEST NUMBER: P584941
 CATALOG NUMBER: HCC8S55D010MW-HM82555830-81WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	301.9	5.7
10°-20°	886.4	16.7
20°-30°	1549.8	29.2
30°-40°	1507.6	28.4
40°-50°	685.6	12.9
50°-60°	317.9	6.0
60°-70°	53.3	1.0
70°-80°	6.5	0.1
80°-90°	2.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2738.2	51.6
0°-40°	4245.8	79.9
0°-60°	5249.3	98.8
0°-90°	5311.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5311.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3227	
5°	3188	302
15°	3085	886
25°	3419	1550
35°	2532	1508
45°	841	686
55°	351	318
65°	39	53
75°	7	7
85°	4	2
90°	0	



TEST NUMBER: P584941
CATALOG NUMBER: HCC8S55D010MW-HM82555830-81WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	3227.3
2.5°	3220.2
5°	3188.3
7.5°	3152.8
10°	3110.3
12.5°	3078.4
15°	3085.4
17.5°	3142.2
20°	3241.5
22.5°	3355.0
25°	3418.8
27.5°	3383.3
30°	3227.3
32.5°	2954.3
35°	2532.2
37.5°	1950.6
40°	1393.7
42.5°	1039.1
45°	840.6
47.5°	709.3
50°	592.2
52.5°	471.7
55°	351.1
57.5°	241.2
60°	149.0
62.5°	81.6
65°	39.0
67.5°	17.7
70°	10.7
72.5°	7.1
75°	7.1
77.5°	3.5
80°	3.5
82.5°	3.5
85°	3.5
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)