

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584954

Luminaire Tested: **HCC8S55D010MB-HM82555835-81NDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584954
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S55D010MB-HM82555835-81NDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5032.7 lumens
Efficiency: N/A
Efficacy: 96.8 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.92
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 52
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584954
CATALOG NUMBER: HCC8S55D010MB-HM82555835-81NDW

Luminous Intensity Polar Plot





TEST NUMBER: P584954

CATALOG NUMBER: HCC8S55D010MB-HM82555835-81NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			
2	105	99	94	90	102	97	92	88	94	90	87	91	87	85	88	85	83	81			
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73			
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	72	68	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	76	66	59	54	64	58	54	63	58	54	62	57	53	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	58	51	47	68	57	51	47	56	51	46	55	50	46	55	50	46	45			
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125442
5°	125110
10°	123022
15°	121225
20°	118316
25°	112317
30°	92638
35°	47695
40°	31933
45°	27378
50°	23627
55°	20618
60°	18317
65°	16461
70°	14921
75°	13427
80°	12004
85°	11994



TEST NUMBER: P584954
 CATALOG NUMBER: HCC8S55D010MB-HM82555835-81NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	382.1	7.6
10°-20°	1068.4	21.2
20°-30°	1480.3	29.4
30°-40°	889.1	17.7
40°-50°	486.7	9.7
50°-60°	345.8	6.9
60°-70°	224.5	4.5
70°-80°	119.9	2.4
80°-90°	35.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2930.8	58.2
0°-40°	3819.9	75.9
0°-60°	4652.4	92.4
0°-90°	5032.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5032.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4068	
5°	4042	382
15°	3797	1068
25°	3301	1480
35°	1267	889
45°	628	487
55°	384	346
65°	226	224
75°	113	120
85°	34	36
90°	0	



TEST NUMBER: P584954
CATALOG NUMBER: HCC8S55D010MB-HM82555835-81NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4068.0
2.5°	4060.5
5°	4041.8
7.5°	3996.6
10°	3928.9
12.5°	3865.0
15°	3797.3
17.5°	3710.9
20°	3605.5
22.5°	3477.8
25°	3301.1
27.5°	3022.8
30°	2601.7
32.5°	1906.1
35°	1267.0
37.5°	936.2
40°	793.3
42.5°	703.1
45°	627.8
47.5°	556.5
50°	492.5
52.5°	432.4
55°	383.5
57.5°	338.4
60°	297.0
62.5°	259.4
65°	225.6
67.5°	191.7
70°	165.5
72.5°	135.4
75°	112.7
77.5°	90.2
80°	67.6
82.5°	48.9
85°	33.9
87.5°	15.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)