

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584951

Luminaire Tested: **HCC8S55D010MW-HM82555835-81MDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584951
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S55D010MW-HM82555835-81MDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5566.4 lumens
Efficiency: N/A
Efficacy: 107.0 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.95
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 52
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584951
CATALOG NUMBER: HCC8S55D010MW-HM82555835-81MDW

Luminous Intensity Polar Plot





TEST NUMBER: P584951
 CATALOG NUMBER: HCC8S55D010MW-HM82555835-81MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92		90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82		80
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74		72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67		65
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61		59
6	81	70	63	58	79	69	62	57	67	61	57	66	61	56	64	60	56		54
7	76	65	58	53	74	64	57	53	63	57	52	62	56	52	60	55	52		50
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48		46
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45		43
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42		40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	142334
5°	138455
10°	130289
15°	123355
20°	118660
25°	114079
30°	101315
35°	64522
40°	36011
45°	30160
50°	27229
55°	25666
60°	23411
65°	21116
70°	18636
75°	16573
80°	14686
85°	13303



TEST NUMBER: P584951
 CATALOG NUMBER: HCC8S55D010MW-HM82555835-81MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	417.0	7.5
10°-20°	1089.7	19.6
20°-30°	1520.3	27.3
30°-40°	1093.9	19.7
40°-50°	542.1	9.7
50°-60°	424.2	7.6
60°-70°	287.1	5.2
70°-80°	149.1	2.7
80°-90°	42.9	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3027.0	54.4
0°-40°	4120.9	74.0
0°-60°	5087.2	91.4
0°-90°	5566.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5566.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4616	
5°	4473	417
15°	3864	1090
25°	3353	1520
35°	1714	1094
45°	692	542
55°	477	424
65°	289	287
75°	139	149
85°	38	43
90°	0	



TEST NUMBER: P584951
CATALOG NUMBER: HCC8S55D010MW-HM82555835-81MDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	4615.8
2.5°	4574.4
5°	4472.9
7.5°	4330.1
10°	4161.0
12.5°	4003.1
15°	3864.0
17.5°	3732.5
20°	3616.0
22.5°	3499.4
25°	3352.9
27.5°	3142.4
30°	2845.4
32.5°	2379.3
35°	1714.0
37.5°	1169.0
40°	894.6
42.5°	770.6
45°	691.6
47.5°	624.0
50°	567.6
52.5°	518.7
55°	477.4
57.5°	428.5
60°	379.6
62.5°	330.7
65°	289.4
67.5°	248.1
70°	206.7
72.5°	172.9
75°	139.1
77.5°	109.0
80°	82.7
82.5°	60.1
85°	37.6
87.5°	18.8
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)