

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593822

Luminaire Tested: **HCC8W55D010SL-HM82555850-81WDBB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P593822  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W55D010SL-HM82555850-81WDBB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6097.9 lumens  
Efficiency: N/A  
Efficacy: 117.3 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 52  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P593822  
CATALOG NUMBER: HCC8W55D010SL-HM82555850-81WDBB

### Luminous Intensity Polar Plot





TEST NUMBER: P593822

CATALOG NUMBER: HCC8W55D010SL-HM82555850-81WDBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	114255
5°	113304
10°	111806
15°	113085
20°	122122
25°	133545
30°	131930
35°	109435
40°	64410
45°	42078
50°	32621
55°	21671
60°	10546
65°	3269
70°	1100
75°	965
80°	728
85°	1451



TEST NUMBER: P593822  
 CATALOG NUMBER: HCC8W55D010SL-HM82555850-81WDBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	346.6	5.7
10°-20°	1017.7	16.7
20°-30°	1779.3	29.2
30°-40°	1730.8	28.4
40°-50°	787.1	12.9
50°-60°	364.9	6.0
60°-70°	61.2	1.0
70°-80°	7.5	0.1
80°-90°	2.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3143.6	51.6
0°-40°	4874.4	79.9
0°-60°	6026.5	98.8
0°-90°	6097.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6097.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3705	
5°	3660	347
15°	3542	1018
25°	3925	1779
35°	2907	1731
45°	965	787
55°	403	365
65°	45	61
75°	8	7
85°	4	3
90°	0	



TEST NUMBER: P593822  
CATALOG NUMBER: HCC8W55D010SL-HM82555850-81WDBB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3705.2
2.5°	3697.0
5°	3660.4
7.5°	3619.6
10°	3570.7
12.5°	3534.2
15°	3542.3
17.5°	3607.4
20°	3721.5
22.5°	3851.7
25°	3925.0
27.5°	3884.2
30°	3705.2
32.5°	3391.7
35°	2907.1
37.5°	2239.3
40°	1600.1
42.5°	1193.0
45°	964.9
47.5°	814.3
50°	680.0
52.5°	541.5
55°	403.1
57.5°	276.8
60°	171.0
62.5°	93.6
65°	44.8
67.5°	20.4
70°	12.2
72.5°	8.1
75°	8.1
77.5°	4.1
80°	4.1
82.5°	4.1
85°	4.1
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)