

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593833

Luminaire Tested: **HCC8S55D010MB-HM82555850-81WDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593833
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S55D010MB-HM82555850-81WDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6252.7 lumens
Efficiency: N/A
Efficacy: 120.2 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 52
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593833
CATALOG NUMBER: HCC8S55D010MB-HM82555850-81WDW

Luminous Intensity Polar Plot





TEST NUMBER: P593833

CATALOG NUMBER: HCC8S55D010MB-HM82555850-81WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125001
5°	124850
10°	123620
15°	122138
20°	121006
25°	119646
30°	112895
35°	91927
40°	50788
45°	33902
50°	30069
55°	28230
60°	27864
65°	27625
70°	24947
75°	22303
80°	19516
85°	17301



TEST NUMBER: P593833
 CATALOG NUMBER: HCC8S55D010MB-HM82555850-81WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	382.3	6.1
10°-20°	1080.3	17.3
20°-30°	1605.2	25.7
30°-40°	1445.5	23.1
40°-50°	640.8	10.2
50°-60°	474.6	7.6
60°-70°	369.1	5.9
70°-80°	200.1	3.2
80°-90°	54.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3067.7	49.1
0°-40°	4513.2	72.2
0°-60°	5628.7	90.0
0°-90°	6252.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6252.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4054	
5°	4033	382
15°	3826	1080
25°	3516	1605
35°	2442	1446
45°	777	641
55°	525	475
65°	379	369
75°	187	200
85°	49	55
90°	0	



TEST NUMBER: P593833
CATALOG NUMBER: HCC8S55D010MB-HM82555850-81WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4053.7
2.5°	4045.6
5°	4033.4
7.5°	4000.9
10°	3948.0
12.5°	3886.9
15°	3825.9
17.5°	3764.8
20°	3687.5
22.5°	3610.1
25°	3516.5
27.5°	3374.1
30°	3170.6
32.5°	2877.5
35°	2442.0
37.5°	1823.4
40°	1261.7
42.5°	932.1
45°	777.4
47.5°	687.8
50°	626.8
52.5°	569.8
55°	525.1
57.5°	488.4
60°	451.8
62.5°	419.2
65°	378.6
67.5°	329.7
70°	276.7
72.5°	231.9
75°	187.2
77.5°	146.5
80°	109.9
82.5°	77.4
85°	48.9
87.5°	20.4
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)