

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585009

Luminaire Tested: **HCC8W55D010MB-HM82555930-81WDBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585009
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W55D010MB-HM82555930-81WDBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5222.5 lumens
Efficiency: N/A
Efficacy: 100.4 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 52
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585009
CATALOG NUMBER: HCC8W55D010MB-HM82555930-81WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P585009

CATALOG NUMBER: HCC8W55D010MB-HM82555930-81WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62			
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	97850
5°	97038
10°	95755
15°	96848
20°	104586
25°	114372
30°	112987
35°	93723
40°	55164
45°	36039
50°	27939
55°	18564
60°	9035
65°	2795
70°	938
75°	834
80°	622
85°	1238



TEST NUMBER: P585009
 CATALOG NUMBER: HCC8W55D010MB-HM82555930-81WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	296.9	5.7
10°-20°	871.5	16.7
20°-30°	1523.8	29.2
30°-40°	1482.3	28.4
40°-50°	674.1	12.9
50°-60°	312.6	6.0
60°-70°	52.4	1.0
70°-80°	6.4	0.1
80°-90°	2.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2692.3	51.6
0°-40°	4174.6	79.9
0°-60°	5161.3	98.8
0°-90°	5222.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5222.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3173	
5°	3135	297
15°	3034	872
25°	3362	1524
35°	2490	1482
45°	826	674
55°	345	313
65°	38	52
75°	7	6
85°	4	2
90°	0	



TEST NUMBER: P585009
CATALOG NUMBER: HCC8W55D010MB-HM82555930-81WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	3173.2
2.5°	3166.2
5°	3134.9
7.5°	3099.9
10°	3058.1
12.5°	3026.7
15°	3033.7
17.5°	3089.5
20°	3187.1
22.5°	3298.7
25°	3361.5
27.5°	3326.6
30°	3173.2
32.5°	2904.7
35°	2489.7
37.5°	1917.9
40°	1370.4
42.5°	1021.7
45°	826.4
47.5°	697.5
50°	582.4
52.5°	463.8
55°	345.3
57.5°	237.1
60°	146.5
62.5°	80.2
65°	38.3
67.5°	17.5
70°	10.4
72.5°	7.0
75°	7.0
77.5°	3.5
80°	3.5
82.5°	3.5
85°	3.5
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)