

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585006

Luminaire Tested: **HCC8W55D010MW-HM82555930-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585006
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W55D010MW-HM82555930-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5184.2 lumens
Efficiency: N/A
Efficacy: 99.7 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 52
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585006
CATALOG NUMBER: HCC8W55D010MW-HM82555930-81PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P585006

CATALOG NUMBER: HCC8W55D010MW-HM82555930-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89		
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71		
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64		
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58		
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53		
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49		
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45		
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42		
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	121686
5°	120102
10°	115704
15°	111179
20°	108107
25°	104852
30°	94087
35°	61680
40°	34099
45°	28429
50°	25920
55°	24736
60°	23004
65°	20861
70°	18861
75°	17037
80°	15485
85°	14789



TEST NUMBER: P585006

CATALOG NUMBER: HCC8W55D010MW-HM82555930-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	364.6	7.0
10°-20°	982.5	19.0
20°-30°	1398.3	27.0
30°-40°	1034.9	20.0
40°-50°	512.6	9.9
50°-60°	409.1	7.9
60°-70°	284.0	5.5
70°-80°	153.1	3.0
80°-90°	45.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2745.4	53.0
0°-40°	3780.3	72.9
0°-60°	4702.0	90.7
0°-90°	5184.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5184.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3946	
5°	3880	365
15°	3483	983
25°	3082	1398
35°	1638	1035
45°	652	513
55°	460	409
65°	286	284
75°	143	153
85°	42	45
90°	0	



TEST NUMBER: P585006
CATALOG NUMBER: HCC8W55D010MW-HM82555930-81PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3946.2
2.5°	3928.8
5°	3880.0
7.5°	3803.3
10°	3695.2
12.5°	3583.6
15°	3482.6
17.5°	3385.0
20°	3294.4
22.5°	3203.7
25°	3081.7
27.5°	2903.9
30°	2642.4
32.5°	2241.6
35°	1638.5
37.5°	1119.0
40°	847.1
42.5°	725.1
45°	651.9
47.5°	592.7
50°	540.3
52.5°	495.1
55°	460.1
57.5°	418.3
60°	373.0
62.5°	327.7
65°	285.9
67.5°	244.0
70°	209.2
72.5°	174.3
75°	143.0
77.5°	115.1
80°	87.2
82.5°	62.7
85°	41.8
87.5°	17.5
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)