

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585026

Luminaire Tested: **HCC8S55D010BZ-HM82555935-81WDBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585026
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S55D010BZ-HM82555935-81WDBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5250.5 lumens
Efficiency: N/A
Efficacy: 101.0 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 52
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585026
CATALOG NUMBER: HCC8S55D010BZ-HM82555935-81WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P585026

CATALOG NUMBER: HCC8S55D010BZ-HM82555935-81WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92	92
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83	83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75	75
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68	68
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62	62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51	51
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47	47
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43	43
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	98377
5°	97558
10°	96272
15°	97369
20°	105147
25°	114988
30°	113596
35°	94231
40°	55462
45°	36230
50°	28083
55°	18655
60°	9078
65°	2816
70°	947
75°	834
80°	622
85°	1238



TEST NUMBER: P585026
 CATALOG NUMBER: HCC8S55D010BZ-HM82555935-81WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	298.5	5.7
10°-20°	876.2	16.7
20°-30°	1532.0	29.2
30°-40°	1490.3	28.4
40°-50°	677.8	12.9
50°-60°	314.2	6.0
60°-70°	52.7	1.0
70°-80°	6.5	0.1
80°-90°	2.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2706.8	51.6
0°-40°	4197.1	79.9
0°-60°	5189.0	98.8
0°-90°	5250.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5250.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3190	
5°	3152	298
15°	3050	876
25°	3380	1532
35°	2503	1490
45°	831	678
55°	347	314
65°	39	53
75°	7	6
85°	4	2
90°	0	



TEST NUMBER: P585026
CATALOG NUMBER: HCC8S55D010BZ-HM82555935-81WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	3190.3
2.5°	3183.3
5°	3151.7
7.5°	3116.7
10°	3074.6
12.5°	3043.0
15°	3050.0
17.5°	3106.2
20°	3204.2
22.5°	3316.5
25°	3379.6
27.5°	3344.5
30°	3190.3
32.5°	2920.4
35°	2503.2
37.5°	1928.2
40°	1377.8
42.5°	1027.3
45°	830.8
47.5°	701.2
50°	585.4
52.5°	466.2
55°	347.0
57.5°	238.4
60°	147.2
62.5°	80.6
65°	38.6
67.5°	17.6
70°	10.5
72.5°	7.0
75°	7.0
77.5°	3.5
80°	3.5
82.5°	3.5
85°	3.5
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)