

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585062

Luminaire Tested: **HCC8W60D010MW-HM86080827-81WDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585062
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W60D010MW-HM86080827-81WDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5547.3 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585062
CATALOG NUMBER: HCC8W60D010MW-HM86080827-81WDH

Luminous Intensity Polar Plot





TEST NUMBER: P585062
 CATALOG NUMBER: HCC8W60D010MW-HM86080827-81WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75		
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68		
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62		
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57		
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52		
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48		
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44		
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42	41		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	126993
5°	124135
10°	120329
15°	117896
20°	116836
25°	115090
30°	109021
35°	90579
40°	53341
45°	35280
50°	27771
55°	20440
60°	14191
65°	8654
70°	3778
75°	1668
80°	1225
85°	0



TEST NUMBER: P585062
 CATALOG NUMBER: HCC8W60D010MW-HM86080827-81WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	377.6	6.8
10°-20°	1044.0	18.8
20°-30°	1546.8	27.9
30°-40°	1429.3	25.8
40°-50°	659.0	11.9
50°-60°	346.7	6.2
60°-70°	122.5	2.2
70°-80°	19.3	0.3
80°-90°	1.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2968.5	53.5
0°-40°	4397.9	79.3
0°-60°	5403.6	97.4
0°-90°	5547.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5547.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4118	
5°	4010	378
15°	3693	1044
25°	3383	1547
35°	2406	1429
45°	809	659
55°	380	347
65°	119	123
75°	14	19
85°	0	2
90°	0	



TEST NUMBER: P585062
CATALOG NUMBER: HCC8W60D010MW-HM86080827-81WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4118.3
2.5°	4083.5
5°	4010.3
7.5°	3930.1
10°	3842.9
12.5°	3759.2
15°	3693.0
17.5°	3633.7
20°	3560.4
22.5°	3480.3
25°	3382.6
27.5°	3250.1
30°	3061.8
32.5°	2793.3
35°	2406.2
37.5°	1848.2
40°	1325.1
42.5°	993.9
45°	809.0
47.5°	687.0
50°	578.9
52.5°	474.3
55°	380.2
57.5°	299.9
60°	230.1
62.5°	174.4
65°	118.6
67.5°	69.8
70°	41.9
72.5°	24.5
75°	14.0
77.5°	10.5
80°	6.9
82.5°	3.5
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)