

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585080

Luminaire Tested: **HCC8S60D010BZ-HM86080830-81WDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585080
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S60D010BZ-HM86080830-81WDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5316.6 lumens
Efficiency: N/A
Efficacy: 94.9 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585080
CATALOG NUMBER: HCC8S60D010BZ-HM86080830-81WDW

Luminous Intensity Polar Plot





TEST NUMBER: P585080

CATALOG NUMBER: HCC8S60D010BZ-HM86080830-81WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	106290
5°	106160
10°	105114
15°	103855
20°	102889
25°	101735
30°	95996
35°	78168
40°	43188
45°	28826
50°	25569
55°	24004
60°	23695
65°	23480
70°	21214
75°	18967
80°	16586
85°	14683



TEST NUMBER: P585080
 CATALOG NUMBER: HCC8S60D010BZ-HM86080830-81WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	325.0	6.1
10°-20°	918.6	17.3
20°-30°	1364.9	25.7
30°-40°	1229.1	23.1
40°-50°	544.9	10.2
50°-60°	403.6	7.6
60°-70°	313.8	5.9
70°-80°	170.1	3.2
80°-90°	46.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2608.5	49.1
0°-40°	3837.6	72.2
0°-60°	4786.1	90.0
0°-90°	5316.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5316.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3447	
5°	3430	325
15°	3253	919
25°	2990	1365
35°	2076	1229
45°	661	545
55°	446	404
65°	322	314
75°	159	170
85°	42	47
90°	0	



TEST NUMBER: P585080
CATALOG NUMBER: HCC8S60D010BZ-HM86080830-81WDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3446.9
2.5°	3440.0
5°	3429.6
7.5°	3402.0
10°	3357.0
12.5°	3305.1
15°	3253.2
17.5°	3201.3
20°	3135.4
22.5°	3069.7
25°	2990.1
27.5°	2869.0
30°	2696.0
32.5°	2446.7
35°	2076.5
37.5°	1550.4
40°	1072.9
42.5°	792.5
45°	661.0
47.5°	584.9
50°	533.0
52.5°	484.5
55°	446.5
57.5°	415.3
60°	384.2
62.5°	356.5
65°	321.8
67.5°	280.3
70°	235.3
72.5°	197.2
75°	159.2
77.5°	124.6
80°	93.4
82.5°	65.7
85°	41.5
87.5°	17.3
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)