

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585074

Luminaire Tested: **HCC8S60D010SL-HM86080830-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585074
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S60D010SL-HM86080830-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5147.0 lumens
Efficiency: N/A
Efficacy: 91.9 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585074
CATALOG NUMBER: HCC8S60D010SL-HM86080830-81PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P585074
 CATALOG NUMBER: HCC8S60D010SL-HM86080830-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89		
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71		
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64		
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58		
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53		
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49		
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45		
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42		
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	120817
5°	119241
10°	114874
15°	110384
20°	107332
25°	104100
30°	93414
35°	61240
40°	33858
45°	28224
50°	25733
55°	24564
60°	22844
65°	20715
70°	18717
75°	16906
80°	15361
85°	14683



TEST NUMBER: P585074
 CATALOG NUMBER: HCC8S60D010SL-HM86080830-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	361.9	7.0
10°-20°	975.5	19.0
20°-30°	1388.3	27.0
30°-40°	1027.5	20.0
40°-50°	508.9	9.9
50°-60°	406.2	7.9
60°-70°	282.0	5.5
70°-80°	151.9	3.0
80°-90°	44.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2725.8	53.0
0°-40°	3753.3	72.9
0°-60°	4668.4	90.7
0°-90°	5147.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5147.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3918	
5°	3852	362
15°	3458	976
25°	3060	1388
35°	1627	1028
45°	647	509
55°	457	406
65°	284	282
75°	142	152
85°	42	45
90°	0	



TEST NUMBER: P585074
CATALOG NUMBER: HCC8S60D010SL-HM86080830-81PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3918.0
2.5°	3900.7
5°	3852.2
7.5°	3776.1
10°	3668.7
12.5°	3558.0
15°	3457.7
17.5°	3360.8
20°	3270.8
22.5°	3180.7
25°	3059.6
27.5°	2883.2
30°	2623.5
32.5°	2225.5
35°	1626.8
37.5°	1111.1
40°	841.1
42.5°	720.0
45°	647.2
47.5°	588.3
50°	536.4
52.5°	491.5
55°	456.9
57.5°	415.3
60°	370.4
62.5°	325.4
65°	283.9
67.5°	242.3
70°	207.6
72.5°	173.0
75°	141.9
77.5°	114.2
80°	86.5
82.5°	62.3
85°	41.5
87.5°	17.3
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)