

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585095

Luminaire Tested: **HCC8S60D010MW-HM86080835-81WDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585095
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S60D010MW-HM86080835-81WDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6993.9 lumens
Efficiency: N/A
Efficacy: 124.9 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585095
CATALOG NUMBER: HCC8S60D010MW-HM86080835-81WDC

Luminous Intensity Polar Plot





TEST NUMBER: P585095
 CATALOG NUMBER: HCC8S60D010MW-HM86080835-81WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92			92	
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84			84	
3	100	93	87	83	98	91	86	82	89	84	81	86	83	79	84	81	78	77			77	
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	71	70			70	
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64			64	
6	83	73	66	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59			59	
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	63	59	55	54			54	
8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50			50	
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46			46	
10	66	55	49	45	65	55	49	45	54	48	44	53	48	44	52	48	44	43			43	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	167799
5°	163286
10°	162043
15°	159627
20°	154796
25°	149022
30°	139201
35°	115195
40°	69551
45°	46845
50°	33754
55°	19247
60°	8474
65°	3035
70°	1127
75°	500
80°	0
85°	0



TEST NUMBER: P585095
 CATALOG NUMBER: HCC8S60D010MW-HM86080835-81WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	501.2	7.2
10°-20°	1405.2	20.1
20°-30°	2004.6	28.7
30°-40°	1825.4	26.1
40°-50°	861.1	12.3
50°-60°	338.6	4.8
60°-70°	54.0	0.8
70°-80°	3.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3911.0	55.9
0°-40°	5736.4	82.0
0°-60°	6936.1	99.2
0°-90°	6993.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6993.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5442	
5°	5275	501
15°	5000	1405
25°	4380	2005
35°	3060	1825
45°	1074	861
55°	358	339
65°	42	54
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P585095

CATALOG NUMBER: HCC8S60D010MW-HM86080835-81WDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	5441.6
2.5°	5370.8
5°	5275.1
7.5°	5220.9
10°	5175.1
12.5°	5100.2
15°	5000.2
17.5°	4875.3
20°	4717.2
22.5°	4550.6
25°	4379.9
27.5°	4171.7
30°	3909.4
32.5°	3555.6
35°	3060.1
37.5°	2364.8
40°	1727.8
42.5°	1328.1
45°	1074.2
47.5°	882.7
50°	703.6
52.5°	528.7
55°	358.0
57.5°	224.8
60°	137.4
62.5°	83.3
65°	41.6
67.5°	20.8
70°	12.5
72.5°	4.2
75°	4.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)