

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585091

Luminaire Tested: **HCC8S60D010MW-HM86080835-81PSMDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585091  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S60D010MW-HM86080835-81PSMDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6190.4 lumens  
Efficiency: N/A  
Efficacy: 110.5 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 56  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585091  
CATALOG NUMBER: HCC8S60D010MW-HM86080835-81PSMDW

### Luminous Intensity Polar Plot





TEST NUMBER: P585091

CATALOG NUMBER: HCC8S60D010MW-HM86080835-81PSMDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91		89
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81		79
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73		71
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66		64
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60		58
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55		53
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51		49
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47		45
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44		42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41		39

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	145307
5°	143417
10°	138167
15°	132760
20°	129089
25°	125205
30°	112353
35°	73651
40°	40717
45°	33945
50°	30952
55°	29542
60°	27469
65°	24903
70°	22513
75°	20338
80°	18468
85°	17655



TEST NUMBER: P585091  
 CATALOG NUMBER: HCC8S60D010MW-HM86080835-81PSMDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	435.3	7.0
10°-20°	1173.3	19.0
20°-30°	1669.7	27.0
30°-40°	1235.8	20.0
40°-50°	612.1	9.9
50°-60°	488.5	7.9
60°-70°	339.1	5.5
70°-80°	182.8	3.0
80°-90°	53.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3278.3	53.0
0°-40°	4514.1	72.9
0°-60°	5614.7	90.7
0°-90°	6190.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6190.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4712	
5°	4633	435
15°	4159	1173
25°	3680	1670
35°	1956	1236
45°	778	612
55°	550	489
65°	341	339
75°	171	183
85°	50	54
90°	0	



TEST NUMBER: P585091  
CATALOG NUMBER: HCC8S60D010MW-HM86080835-81PSMDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4712.2
2.5°	4691.5
5°	4633.2
7.5°	4541.6
10°	4412.6
12.5°	4279.3
15°	4158.6
17.5°	4042.1
20°	3933.8
22.5°	3825.6
25°	3679.9
27.5°	3467.6
30°	3155.4
32.5°	2676.7
35°	1956.5
37.5°	1336.2
40°	1011.5
42.5°	865.9
45°	778.4
47.5°	707.7
50°	645.2
52.5°	591.1
55°	549.5
57.5°	499.5
60°	445.4
62.5°	391.3
65°	341.3
67.5°	291.3
70°	249.7
72.5°	208.2
75°	170.7
77.5°	137.4
80°	104.0
82.5°	75.0
85°	49.9
87.5°	20.8
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)