

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585114

Luminaire Tested: **HCC8W60D010BZ-HM86080840-81WDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585114
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W60D010BZ-HM86080840-81WDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6696.6 lumens
Efficiency: N/A
Efficacy: 119.6 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585114
CATALOG NUMBER: HCC8W60D010BZ-HM86080840-81WDW

Luminous Intensity Polar Plot





TEST NUMBER: P585114

CATALOG NUMBER: HCC8W60D010BZ-HM86080840-81WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	133879
5°	133716
10°	132393
15°	130809
20°	129594
25°	128142
30°	120910
35°	98455
40°	54395
45°	36305
50°	32204
55°	30230
60°	29843
65°	29580
70°	26723
75°	23888
80°	20883
85°	18539



TEST NUMBER: P585114
 CATALOG NUMBER: HCC8W60D010BZ-HM86080840-81WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	409.4	6.1
10°-20°	1157.0	17.3
20°-30°	1719.1	25.7
30°-40°	1548.2	23.1
40°-50°	686.3	10.2
50°-60°	508.3	7.6
60°-70°	395.3	5.9
70°-80°	214.3	3.2
80°-90°	58.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3285.5	49.1
0°-40°	4833.6	72.2
0°-60°	6028.3	90.0
0°-90°	6696.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6696.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4342	
5°	4320	409
15°	4098	1157
25°	3766	1719
35°	2615	1548
45°	832	686
55°	562	508
65°	405	395
75°	200	214
85°	52	59
90°	0	



TEST NUMBER: P585114
CATALOG NUMBER: HCC8W60D010BZ-HM86080840-81WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4341.6
2.5°	4332.9
5°	4319.8
7.5°	4284.9
10°	4228.2
12.5°	4162.9
15°	4097.5
17.5°	4032.1
20°	3949.2
22.5°	3866.4
25°	3766.2
27.5°	3613.6
30°	3395.7
32.5°	3081.8
35°	2615.4
37.5°	1952.8
40°	1351.3
42.5°	998.3
45°	832.5
47.5°	736.7
50°	671.3
52.5°	610.3
55°	562.3
57.5°	523.1
60°	483.9
62.5°	449.0
65°	405.4
67.5°	353.1
70°	296.4
72.5°	248.4
75°	200.5
77.5°	157.0
80°	117.6
82.5°	82.8
85°	52.4
87.5°	21.8
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)