

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585128

Luminaire Tested: **HCC8W60D010SL-HM86080927-81WDBB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585128  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W60D010SL-HM86080927-81WDBB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4549.0 lumens  
Efficiency: N/A  
Efficacy: 81.2 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 56  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585128  
CATALOG NUMBER: HCC8W60D010SL-HM86080927-81WDBB

### Luminous Intensity Polar Plot





TEST NUMBER: P585128

CATALOG NUMBER: HCC8W60D010SL-HM86080927-81WDBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	85232
5°	84523
10°	83409
15°	84363
20°	91099
25°	99623
30°	98417
35°	81639
40°	48051
45°	31390
50°	24337
55°	16166
60°	7869
65°	2437
70°	820
75°	727
80°	533
85°	1061



TEST NUMBER: P585128  
 CATALOG NUMBER: HCC8W60D010SL-HM86080927-81WDBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	258.6	5.7
10°-20°	759.2	16.7
20°-30°	1327.3	29.2
30°-40°	1291.2	28.4
40°-50°	587.2	12.9
50°-60°	272.3	6.0
60°-70°	45.6	1.0
70°-80°	5.6	0.1
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2345.1	51.6
0°-40°	3636.3	79.9
0°-60°	4495.7	98.8
0°-90°	4549.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4549.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2764	
5°	2731	259
15°	2643	759
25°	2928	1327
35°	2169	1291
45°	720	587
55°	301	272
65°	33	46
75°	6	6
85°	3	2
90°	0	



TEST NUMBER: P585128  
CATALOG NUMBER: HCC8W60D010SL-HM86080927-81WDBB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2764.0
2.5°	2757.9
5°	2730.6
7.5°	2700.2
10°	2663.8
12.5°	2636.4
15°	2642.6
17.5°	2691.1
20°	2776.1
22.5°	2873.4
25°	2928.0
27.5°	2897.7
30°	2764.0
32.5°	2530.1
35°	2168.7
37.5°	1670.6
40°	1193.7
42.5°	890.0
45°	719.8
47.5°	607.5
50°	507.3
52.5°	403.9
55°	300.7
57.5°	206.6
60°	127.6
62.5°	69.9
65°	33.4
67.5°	15.2
70°	9.1
72.5°	6.1
75°	6.1
77.5°	3.0
80°	3.0
82.5°	3.0
85°	3.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)