

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585123

Luminaire Tested: **HCC8W60D010MW-HM86080927-81NDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585123
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W60D010MW-HM86080927-81NDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4111.6 lumens
Efficiency: N/A
Efficacy: 73.4 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.57
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585123
CATALOG NUMBER: HCC8W60D010MW-HM86080927-81NDH

Luminous Intensity Polar Plot





TEST NUMBER: P585123

CATALOG NUMBER: HCC8W60D010MW-HM86080927-81NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95		
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89		
3	104	99	94	91	102	97	93	90	95	91	88	92	90	87	90	88	86	84		
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	80		
5	96	88	83	79	94	87	82	79	86	81	78	84	80	77	82	79	77	75		
6	92	84	78	75	90	83	78	74	81	77	74	80	76	73	79	76	73	72		
7	88	80	74	71	87	79	74	70	78	73	70	77	73	70	76	72	69	68		
8	84	76	71	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65		
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62		
10	78	69	64	61	77	69	64	61	68	63	60	67	63	60	67	63	60	59		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	327170
5°	277179
10°	201108
15°	151027
20°	119159
25°	96118
30°	71231
35°	28854
40°	12169
45°	6524
50°	2931
55°	1478
60°	937
65°	664
70°	550
75°	357
80°	533
85°	1061



TEST NUMBER: P585123
 CATALOG NUMBER: HCC8W60D010MW-HM86080927-81NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	768.8	18.7
10°-20°	1328.7	32.3
20°-30°	1284.7	31.2
30°-40°	564.2	13.7
40°-50°	121.9	3.0
50°-60°	27.4	0.7
60°-70°	9.4	0.2
70°-80°	3.6	0.1
80°-90°	2.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3382.2	82.3
0°-40°	3946.4	96.0
0°-60°	4095.7	99.6
0°-90°	4111.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4111.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10610	
5°	8954	769
15°	4731	1329
25°	2825	1285
35°	766	564
45°	150	122
55°	28	27
65°	9	9
75°	3	4
85°	3	3
90°	0	



TEST NUMBER: P585123
CATALOG NUMBER: HCC8W60D010MW-HM86080927-81NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	10609.9
1°	10530.4
2°	10313.6
3°	9922.7
4°	9455.5
5°	8954.5
6°	8407.8
7°	7858.1
8°	7342.0
9°	6862.5
10°	6422.7
11°	6007.4
12°	5634.8
13°	5295.7
14°	4996.5
15°	4730.8
17.5°	4135.2
20°	3631.2
22.5°	3188.5
25°	2825.0
27.5°	2455.5
30°	2000.5
32.5°	1359.1
35°	766.5
37.5°	452.0
40°	302.3
42.5°	213.8
45°	149.6
47.5°	97.7
50°	61.1
52.5°	36.7
55°	27.5
57.5°	21.3
60°	15.2
62.5°	12.2
65°	9.1
67.5°	6.1
70°	6.1
72.5°	3.0
75°	3.0
77.5°	3.0
80°	3.0
82.5°	3.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P585123
CATALOG NUMBER: HCC8W60D010MW-HM86080927-81NDH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



85°		3.0
87.5°		3.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)