

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585130

Luminaire Tested: **HCC8W60D010MW-HM86080927-81WDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585130
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W60D010MW-HM86080927-81WDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4831.4 lumens
Efficiency: N/A
Efficacy: 86.3 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585130
CATALOG NUMBER: HCC8W60D010MW-HM86080927-81WDH

Luminous Intensity Polar Plot





TEST NUMBER: P585130
 CATALOG NUMBER: HCC8W60D010MW-HM86080927-81WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	110610
5°	108116
10°	104804
15°	102684
20°	101760
25°	100238
30°	94952
35°	78891
40°	46461
45°	30727
50°	24188
55°	17795
60°	12365
65°	7530
70°	3282
75°	1442
80°	1083
85°	0



TEST NUMBER: P585130
 CATALOG NUMBER: HCC8W60D010MW-HM86080927-81WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	328.9	6.8
10°-20°	909.3	18.8
20°-30°	1347.2	27.9
30°-40°	1244.9	25.8
40°-50°	574.0	11.9
50°-60°	301.9	6.2
60°-70°	106.7	2.2
70°-80°	16.7	0.3
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2585.5	53.5
0°-40°	3830.4	79.3
0°-60°	4706.3	97.4
0°-90°	4831.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4831.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3587	
5°	3493	329
15°	3216	909
25°	2946	1347
35°	2096	1245
45°	705	574
55°	331	302
65°	103	107
75°	12	17
85°	0	2
90°	0	



TEST NUMBER: P585130
CATALOG NUMBER: HCC8W60D010MW-HM86080927-81WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3587.0
2.5°	3556.6
5°	3492.8
7.5°	3422.9
10°	3347.1
12.5°	3274.2
15°	3216.5
17.5°	3164.8
20°	3101.0
22.5°	3031.1
25°	2946.1
27.5°	2830.7
30°	2666.7
32.5°	2432.9
35°	2095.7
37.5°	1609.8
40°	1154.2
42.5°	865.6
45°	704.6
47.5°	598.4
50°	504.2
52.5°	413.0
55°	331.0
57.5°	261.2
60°	200.5
62.5°	151.9
65°	103.2
67.5°	60.8
70°	36.4
72.5°	21.2
75°	12.1
77.5°	9.1
80°	6.1
82.5°	3.0
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)