

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585125

Luminaire Tested: **HCC8W60D010MW-HM86080927-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585125
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W60D010MW-HM86080927-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4515.6 lumens
Efficiency: N/A
Efficacy: 80.6 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585125
CATALOG NUMBER: HCC8W60D010MW-HM86080927-81PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P585125

CATALOG NUMBER: HCC8W60D010MW-HM86080927-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89			89
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79			79
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71			71
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64			64
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58			58
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49			49
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45			45
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42			42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39			39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	105997
5°	104616
10°	100784
15°	96839
20°	94164
25°	91331
30°	81956
35°	53726
40°	29699
45°	24761
50°	22581
55°	21548
60°	20037
65°	18168
70°	16427
75°	14833
80°	13478
85°	12879



TEST NUMBER: P585125

CATALOG NUMBER: HCC8W60D010MW-HM86080927-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	317.5	7.0
10°-20°	855.8	19.0
20°-30°	1218.0	27.0
30°-40°	901.5	20.0
40°-50°	446.5	9.9
50°-60°	356.3	7.9
60°-70°	247.4	5.5
70°-80°	133.3	3.0
80°-90°	39.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2391.4	53.0
0°-40°	3292.8	72.9
0°-60°	4095.6	90.7
0°-90°	4515.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4515.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3437	
5°	3380	318
15°	3033	856
25°	2684	1218
35°	1427	901
45°	568	446
55°	401	356
65°	249	247
75°	124	133
85°	36	39
90°	0	



TEST NUMBER: P585125

CATALOG NUMBER: HCC8W60D010MW-HM86080927-81PSMDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3437.4
2.5°	3422.1
5°	3379.7
7.5°	3312.9
10°	3218.7
12.5°	3121.6
15°	3033.4
17.5°	2948.4
20°	2869.5
22.5°	2790.5
25°	2684.3
27.5°	2529.4
30°	2301.7
32.5°	1952.5
35°	1427.2
37.5°	974.7
40°	737.8
42.5°	631.6
45°	567.8
47.5°	516.3
50°	470.7
52.5°	431.1
55°	400.8
57.5°	364.4
60°	324.9
62.5°	285.5
65°	249.0
67.5°	212.6
70°	182.2
72.5°	151.8
75°	124.5
77.5°	100.2
80°	75.9
82.5°	54.7
85°	36.4
87.5°	15.2
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)