

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585132

Luminaire Tested: **HCC8W60D010SL-HM86080927-81WDWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585132
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W60D010SL-HM86080927-81WDWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5001.5 lumens
Efficiency: N/A
Efficacy: 89.3 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585132
CATALOG NUMBER: HCC8W60D010SL-HM86080927-81WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P585132
 CATALOG NUMBER: HCC8W60D010SL-HM86080927-81WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51	49
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	47	43	41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	87840
5°	87232
10°	87007
15°	89289
20°	96664
25°	103634
30°	101315
35°	84368
40°	51835
45°	35890
50°	27388
55°	17956
60°	11237
65°	8427
70°	8484
75°	9770
80°	10797
85°	9659



TEST NUMBER: P585132
 CATALOG NUMBER: HCC8W60D010SL-HM86080927-81WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	267.8	5.4
10°-20°	802.9	16.1
20°-30°	1382.2	27.6
30°-40°	1339.1	26.8
40°-50°	659.6	13.2
50°-60°	311.2	6.2
60°-70°	122.7	2.5
70°-80°	84.6	1.7
80°-90°	31.4	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2452.9	49.0
0°-40°	3792.0	75.8
0°-60°	4762.8	95.2
0°-90°	5001.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5001.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2849	
5°	2818	268
15°	2797	803
25°	3046	1382
35°	2241	1339
45°	823	660
55°	334	311
65°	116	123
75°	82	85
85°	27	31
90°	0	



TEST NUMBER: P585132
CATALOG NUMBER: HCC8W60D010SL-HM86080927-81WDWB

CANDELA DISTRIBUTION (FULL):

0°	
0°	2848.6
2.5°	2839.4
5°	2818.1
7.5°	2796.9
10°	2778.7
12.5°	2775.7
15°	2796.9
17.5°	2860.7
20°	2945.7
22.5°	3021.7
25°	3045.9
27.5°	2991.2
30°	2845.4
32.5°	2605.5
35°	2241.2
37.5°	1740.1
40°	1287.7
42.5°	999.1
45°	823.0
47.5°	692.4
50°	570.9
52.5°	449.5
55°	334.0
57.5°	242.9
60°	182.2
62.5°	142.7
65°	115.5
67.5°	100.2
70°	94.1
72.5°	88.1
75°	82.0
77.5°	72.9
80°	60.8
82.5°	45.6
85°	27.3
87.5°	12.1
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)