

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585136

Luminaire Tested: **HCC8S60D010BZ-HM86080930-81MDC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585136  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S60D010BZ-HM86080930-81MDC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5249.9 lumens  
Efficiency: N/A  
Efficacy: 93.7 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.67  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 56  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585136  
CATALOG NUMBER: HCC8S60D010BZ-HM86080930-81MDC

### Luminous Intensity Polar Plot





TEST NUMBER: P585136  
 CATALOG NUMBER: HCC8S60D010BZ-HM86080930-81MDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94	92	91	89
3	104	98	94	90	102	97	93	90	94	91	88		92	89	87		90	87	85	84
4	100	93	88	84	98	92	87	83	90	86	82		88	84	82		86	83	81	79
5	95	88	82	78	94	87	82	78	85	81	77		83	80	77		82	79	76	75
6	91	83	78	74	90	82	77	74	81	76	73		79	76	73		78	75	72	71
7	87	79	73	70	86	78	73	69	77	72	69		76	72	69		75	71	68	67
8	84	75	70	66	82	74	69	66	73	69	65		72	68	65		71	68	65	64
9	80	71	66	62	79	71	66	62	70	65	62		69	65	62		68	65	62	61
10	77	68	63	59	76	68	63	59	67	62	59		66	62	59		65	62	59	58

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	313673
5°	299283
10°	258390
15°	197581
20°	151177
25°	119605
30°	90348
35°	48064
40°	18307
45°	8783
50°	3742
55°	1575
60°	604
65°	474
70°	289
75°	0
80°	0
85°	0



TEST NUMBER: P585136  
 CATALOG NUMBER: HCC8S60D010BZ-HM86080930-81MDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	877.7	16.7
10°-20°	1727.8	32.9
20°-30°	1609.2	30.7
30°-40°	830.3	15.8
40°-50°	169.1	3.2
50°-60°	28.9	0.6
60°-70°	5.6	0.1
70°-80°	1.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4214.6	80.3
0°-40°	5045.0	96.1
0°-60°	5243.0	99.9
0°-90°	5249.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5249.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10172	
5°	9669	878
15°	6189	1728
25°	3515	1609
35°	1277	830
45°	201	169
55°	29	29
65°	6	6
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P585136  
CATALOG NUMBER: HCC8S60D010BZ-HM86080930-81MDC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	10172.2
2.5°	10035.7
5°	9668.6
7.5°	9064.3
10°	8252.1
12.5°	7186.5
15°	6189.1
17.5°	5324.9
20°	4606.9
22.5°	4022.1
25°	3515.3
27.5°	3034.5
30°	2537.4
32.5°	1946.1
35°	1276.8
37.5°	740.7
40°	454.8
42.5°	298.8
45°	201.4
47.5°	126.8
50°	78.0
52.5°	45.4
55°	29.3
57.5°	13.0
60°	9.8
62.5°	6.5
65°	6.5
67.5°	3.2
70°	3.2
72.5°	3.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)