

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585146

Luminaire Tested: **HCC8S60D010BZ-HM86080930-81WDC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585146  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-7)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S60D010BZ-HM86080930-81WDC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5457.8 lumens  
Efficiency: N/A  
Efficacy: 97.5 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.05  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 56  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585146  
CATALOG NUMBER: HCC8S60D010BZ-HM86080930-81WDC

### Luminous Intensity Polar Plot





TEST NUMBER: P585146  
 CATALOG NUMBER: HCC8S60D010BZ-HM86080930-81WDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96	95	94	92
2	106	101	96	93	104	99	95	92	96	92	90		93	90	88		90	88	86	84
3	100	93	87	83	98	91	86	82	89	84	81		86	83	79		84	81	78	77
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78	75	71	70
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73	69	65	64
6	83	73	66	62	82	72	66	61	71	65	61		69	64	61		68	64	60	59
7	78	68	61	57	77	67	61	56	66	60	56		65	60	56		63	59	55	54
8	74	63	57	52	73	63	56	52	62	56	52		60	55	51		59	55	51	50
9	70	59	53	48	69	59	52	48	58	52	48		57	51	48		56	51	47	46
10	66	55	49	45	65	55	49	45	54	48	44		53	48	44		52	48	44	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	130946
5°	127423
10°	126454
15°	124571
20°	120796
25°	116294
30°	108625
35°	89894
40°	54274
45°	36558
50°	26342
55°	15026
60°	6617
65°	2371
70°	884
75°	381
80°	0
85°	0



TEST NUMBER: P585146  
 CATALOG NUMBER: HCC8S60D010BZ-HM86080930-81WDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	391.1	7.2
10°-20°	1096.6	20.1
20°-30°	1564.3	28.7
30°-40°	1424.5	26.1
40°-50°	672.0	12.3
50°-60°	264.3	4.8
60°-70°	42.1	0.8
70°-80°	3.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3052.0	55.9
0°-40°	4476.5	82.0
0°-60°	5412.7	99.2
0°-90°	5457.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5457.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4246	
5°	4116	391
15°	3902	1097
25°	3418	1564
35°	2388	1424
45°	838	672
55°	280	264
65°	32	42
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P585146  
CATALOG NUMBER: HCC8S60D010BZ-HM86080930-81WDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4246.5
2.5°	4191.2
5°	4116.5
7.5°	4074.3
10°	4038.5
12.5°	3980.0
15°	3902.1
17.5°	3804.6
20°	3681.1
22.5°	3551.1
25°	3418.0
27.5°	3255.5
30°	3050.7
32.5°	2774.6
35°	2388.0
37.5°	1845.4
40°	1348.3
42.5°	1036.4
45°	838.3
47.5°	688.8
50°	549.1
52.5°	412.6
55°	279.5
57.5°	175.4
60°	107.3
62.5°	64.9
65°	32.5
67.5°	16.3
70°	9.8
72.5°	3.2
75°	3.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)