

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585154

Luminaire Tested: **HCC8S60D010BZ-HM86080935-81MDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585154
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S60D010BZ-HM86080935-81MDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5455.9 lumens
Efficiency: N/A
Efficacy: 97.4 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.81
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585154
CATALOG NUMBER: HCC8S60D010BZ-HM86080935-81MDH

Luminous Intensity Polar Plot





TEST NUMBER: P585154
 CATALOG NUMBER: HCC8S60D010BZ-HM86080935-81MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97	96	95	94
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92	90	89	87
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88	85	83	81
4	97	90	85	80	96	89	84	80	87	82	79		85	81	78		83	80	77	76
5	93	84	79	74	91	83	78	74	82	77	73		80	76	73		78	75	72	71
6	88	79	73	69	87	78	73	69	77	72	68		76	71	68		74	70	67	66
7	84	75	69	64	82	74	68	64	73	68	64		71	67	64		70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67	63	60	58
9	76	67	61	57	75	66	61	57	65	60	56		64	60	56		63	59	56	55
10	73	63	57	54	72	63	57	53	62	57	53		61	56	53		60	56	53	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	249515
5°	227373
10°	194272
15°	169418
20°	151003
25°	133946
30°	109669
35°	62979
40°	27948
45°	16266
50°	9388
55°	5365
60°	2960
65°	1882
70°	1334
75°	882
80°	657
85°	1309



TEST NUMBER: P585154
 CATALOG NUMBER: HCC8S60D010BZ-HM86080935-81MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	664.9	12.2
10°-20°	1491.7	27.3
20°-30°	1785.6	32.7
30°-40°	1080.2	19.8
40°-50°	302.7	5.5
50°-60°	94.0	1.7
60°-70°	26.8	0.5
70°-80°	7.3	0.1
80°-90°	2.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3942.3	72.3
0°-40°	5022.5	92.1
0°-60°	5419.3	99.3
0°-90°	5455.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5455.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8092	
5°	7346	665
15°	5307	1492
25°	3937	1786
35°	1673	1080
45°	373	303
55°	100	94
65°	26	27
75°	7	7
85°	4	3
90°	0	



TEST NUMBER: P585154
CATALOG NUMBER: HCC8S60D010BZ-HM86080935-81MDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	8091.6
2.5°	7862.5
5°	7345.5
7.5°	6762.0
10°	6204.4
12.5°	5716.8
15°	5306.9
17.5°	4945.0
20°	4601.6
22.5°	4284.0
25°	3936.8
27.5°	3545.3
30°	3080.0
32.5°	2478.1
35°	1673.0
37.5°	1041.4
40°	694.3
42.5°	498.6
45°	373.0
47.5°	273.2
50°	195.7
52.5°	136.7
55°	99.8
57.5°	66.4
60°	48.0
62.5°	33.2
65°	25.8
67.5°	18.5
70°	14.8
72.5°	7.4
75°	7.4
77.5°	3.7
80°	3.7
82.5°	3.7
85°	3.7
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)