

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585153

Luminaire Tested: **HCC8S60D010MW-HM86080935-81MDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585153
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S60D010MW-HM86080935-81MDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5969.4 lumens
Efficiency: N/A
Efficacy: 106.6 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.67
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585153
CATALOG NUMBER: HCC8S60D010MW-HM86080935-81MDC

Luminous Intensity Polar Plot





TEST NUMBER: P585153

CATALOG NUMBER: HCC8S60D010MW-HM86080935-81MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94	92	91	89
3	104	98	94	90	102	97	93	90	94	91	88		92	89	87		90	87	85	84
4	100	93	88	84	98	92	87	83	90	86	82		88	84	82		86	83	81	79
5	95	88	82	78	94	87	82	78	85	81	77		83	80	77		82	79	76	75
6	91	83	78	74	90	82	77	73	81	76	73		79	76	73		78	75	72	71
7	87	79	73	70	86	78	73	69	77	72	69		76	72	69		75	71	68	67
8	84	75	70	66	82	74	69	66	73	69	65		72	68	65		71	68	65	64
9	80	71	66	62	79	71	66	62	70	65	62		69	65	62		68	65	62	61
10	77	68	63	59	76	68	63	59	67	62	59		66	62	59		65	62	59	58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	356662
5°	340297
10°	293801
15°	224656
20°	171896
25°	135994
30°	102729
35°	54652
40°	20819
45°	9991
50°	4255
55°	1785
60°	685
65°	540
70°	334
75°	0
80°	0
85°	0



TEST NUMBER: P585153
 CATALOG NUMBER: HCC8S60D010MW-HM86080935-81MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	997.9	16.7
10°-20°	1964.6	32.9
20°-30°	1829.7	30.7
30°-40°	944.1	15.8
40°-50°	192.3	3.2
50°-60°	32.9	0.6
60°-70°	6.4	0.1
70°-80°	1.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4792.2	80.3
0°-40°	5736.3	96.1
0°-60°	5961.6	99.9
0°-90°	5969.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5969.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11566	
5°	10994	998
15°	7037	1965
25°	3997	1830
35°	1452	944
45°	229	192
55°	33	33
65°	7	6
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P585153
CATALOG NUMBER: HCC8S60D010MW-HM86080935-81MDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	11566.3
2.5°	11411.0
5°	10993.6
7.5°	10306.6
10°	9383.0
12.5°	8171.4
15°	7037.2
17.5°	6054.7
20°	5238.3
22.5°	4573.3
25°	3997.0
27.5°	3450.3
30°	2885.1
32.5°	2212.8
35°	1451.8
37.5°	842.2
40°	517.2
42.5°	339.9
45°	229.1
47.5°	144.1
50°	88.7
52.5°	51.7
55°	33.2
57.5°	14.8
60°	11.1
62.5°	7.4
65°	7.4
67.5°	3.7
70°	3.7
72.5°	3.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)