

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585159

Luminaire Tested: **HCC8S60D010MW-HM86080935-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585159
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S60D010MW-HM86080935-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5492.9 lumens
Efficiency: N/A
Efficacy: 98.1 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585159
CATALOG NUMBER: HCC8S60D010MW-HM86080935-81PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P585159
 CATALOG NUMBER: HCC8S60D010MW-HM86080935-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91		89
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81		79
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73		71
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66		64
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60		58
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55		53
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51		49
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47		45
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44		42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41		39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	128933
5°	127255
10°	122596
15°	117800
20°	114542
25°	111096
30°	99692
35°	65350
40°	36132
45°	30125
50°	27464
55°	26209
60°	24379
65°	22101
70°	19979
75°	18038
80°	16408
85°	15674



TEST NUMBER: P585159
 CATALOG NUMBER: HCC8S60D010MW-HM86080935-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	386.3	7.0
10°-20°	1041.1	19.0
20°-30°	1481.6	27.0
30°-40°	1096.6	20.0
40°-50°	543.1	9.9
50°-60°	433.5	7.9
60°-70°	300.9	5.5
70°-80°	162.2	3.0
80°-90°	47.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2908.9	53.0
0°-40°	4005.5	72.9
0°-60°	4982.1	90.7
0°-90°	5492.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5492.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4181	
5°	4111	386
15°	3690	1041
25°	3265	1482
35°	1736	1097
45°	691	543
55°	488	433
65°	303	301
75°	151	162
85°	44	48
90°	0	



TEST NUMBER: P585159
CATALOG NUMBER: HCC8S60D010MW-HM86080935-81PSMDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	4181.2
2.5°	4162.7
5°	4111.1
7.5°	4029.7
10°	3915.3
12.5°	3797.1
15°	3690.0
17.5°	3586.6
20°	3490.5
22.5°	3394.5
25°	3265.2
27.5°	3076.8
30°	2799.8
32.5°	2375.1
35°	1736.0
37.5°	1185.7
40°	897.6
42.5°	768.3
45°	690.8
47.5°	627.9
50°	572.5
52.5°	524.5
55°	487.5
57.5°	443.3
60°	395.3
62.5°	347.2
65°	302.9
67.5°	258.6
70°	221.6
72.5°	184.7
75°	151.4
77.5°	121.9
80°	92.4
82.5°	66.4
85°	44.3
87.5°	18.5
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)