

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585181

Luminaire Tested: **HCC8W60D010MW-HM86080940-81WDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585181
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W60D010MW-HM86080940-81WDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6061.8 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585181
CATALOG NUMBER: HCC8W60D010MW-HM86080940-81WDH

Luminous Intensity Polar Plot





TEST NUMBER: P585181
 CATALOG NUMBER: HCC8W60D010MW-HM86080940-81WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93		92
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85		83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77		75
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70		68
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64		62
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58		57
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54		52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49		48
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46		44
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42		41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	138785
5°	135656
10°	131495
15°	128836
20°	127681
25°	125770
30°	119136
35°	98985
40°	58292
45°	38555
50°	30348
55°	22327
60°	15517
65°	9449
70°	4120
75°	1811
80°	1350
85°	0



TEST NUMBER: P585181
 CATALOG NUMBER: HCC8W60D010MW-HM86080940-81WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	412.7	6.8
10°-20°	1140.9	18.8
20°-30°	1690.4	27.9
30°-40°	1562.0	25.8
40°-50°	720.2	11.9
50°-60°	378.8	6.2
60°-70°	133.8	2.2
70°-80°	21.0	0.3
80°-90°	2.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3244.0	53.5
0°-40°	4806.0	79.3
0°-60°	5904.9	97.4
0°-90°	6061.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6061.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4501	
5°	4382	413
15°	4036	1141
25°	3696	1690
35°	2630	1562
45°	884	720
55°	415	379
65°	130	134
75°	15	21
85°	0	2
90°	0	



TEST NUMBER: P585181
CATALOG NUMBER: HCC8W60D010MW-HM86080940-81WDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4500.7
2.5°	4462.5
5°	4382.5
7.5°	4294.8
10°	4199.5
12.5°	4108.1
15°	4035.7
17.5°	3970.9
20°	3890.9
22.5°	3803.2
25°	3696.5
27.5°	3551.8
30°	3345.9
32.5°	3052.5
35°	2629.5
37.5°	2019.7
40°	1448.1
42.5°	1086.0
45°	884.1
47.5°	750.7
50°	632.6
52.5°	518.2
55°	415.3
57.5°	327.7
60°	251.6
62.5°	190.5
65°	129.5
67.5°	76.2
70°	45.7
72.5°	26.6
75°	15.2
77.5°	11.4
80°	7.6
82.5°	3.8
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)