

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593875

Luminaire Tested: **HCC8S60D010MW-HM86080950-81MDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593875
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S60D010MW-HM86080950-81MDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5627.6 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.81
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593875
CATALOG NUMBER: HCC8S60D010MW-HM86080950-81MDH

Luminous Intensity Polar Plot





TEST NUMBER: P593875
 CATALOG NUMBER: HCC8S60D010MW-HM86080950-81MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94				
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87				
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81				
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76				
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71				
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66				
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62				
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58				
9	76	67	61	57	75	66	61	57	65	60	57	64	60	56	63	59	56	55				
10	73	63	57	54	72	63	57	53	62	57	53	61	56	53	60	56	53	52				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	257366
5°	234533
10°	200384
15°	174753
20°	155758
25°	138165
30°	113119
35°	64959
40°	28826
45°	16781
50°	9681
55°	5532
60°	3053
65°	1941
70°	1370
75°	905
80°	675
85°	1344



TEST NUMBER: P593875
 CATALOG NUMBER: HCC8S60D010MW-HM86080950-81MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	685.8	12.2
10°-20°	1538.7	27.3
20°-30°	1841.8	32.7
30°-40°	1114.2	19.8
40°-50°	312.3	5.5
50°-60°	96.9	1.7
60°-70°	27.6	0.5
70°-80°	7.5	0.1
80°-90°	2.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4066.4	72.3
0°-40°	5180.6	92.1
0°-60°	5589.8	99.3
0°-90°	5627.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5627.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8346	
5°	7577	686
15°	5474	1539
25°	4061	1842
35°	1726	1114
45°	385	312
55°	103	97
65°	27	28
75°	8	7
85°	4	3
90°	0	



TEST NUMBER: P593875
CATALOG NUMBER: HCC8S60D010MW-HM86080950-81MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	8346.2
2.5°	8110.0
5°	7576.8
7.5°	6974.8
10°	6399.6
12.5°	5896.9
15°	5474.0
17.5°	5100.7
20°	4746.5
22.5°	4418.8
25°	4060.8
27.5°	3657.0
30°	3176.9
32.5°	2556.0
35°	1725.6
37.5°	1074.3
40°	716.1
42.5°	514.3
45°	384.8
47.5°	281.9
50°	201.8
52.5°	140.9
55°	102.9
57.5°	68.5
60°	49.5
62.5°	34.3
65°	26.6
67.5°	19.0
70°	15.2
72.5°	7.6
75°	7.6
77.5°	3.8
80°	3.8
82.5°	3.8
85°	3.8
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)