

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585198

Luminaire Tested: **HCC8W80D010MW-HM86080827-81WDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585198
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W80D010MW-HM86080827-81WDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6625.9 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 70
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585198
CATALOG NUMBER: HCC8W80D010MW-HM86080827-81WDH

Luminous Intensity Polar Plot





TEST NUMBER: P585198
 CATALOG NUMBER: HCC8W80D010MW-HM86080827-81WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96	95	93	92
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83	80	77	75
4	93	84	78	73	91	83	77	72	81	76	72		79	74	71		77	73	70	68
5	87	78	71	66	86	77	70	66	75	69	65		73	68	64		71	67	64	62
6	82	72	65	60	80	71	64	60	69	64	59		68	63	59		66	62	58	57
7	77	67	60	55	76	66	59	55	64	59	54		63	58	54		62	57	54	52
8	73	62	55	50	71	61	55	50	60	54	50		59	54	50		58	53	49	48
9	69	58	51	46	67	57	51	46	56	50	46		55	50	46		54	49	46	44
10	65	54	47	43	64	53	47	43	53	47	43		52	46	43		51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	151696
5°	148276
10°	143732
15°	140824
20°	139560
25°	137474
30°	130221
35°	108197
40°	63718
45°	42144
50°	33168
55°	24413
60°	16954
65°	10332
70°	4499
75°	1978
80°	1474
85°	0



TEST NUMBER: P585198
 CATALOG NUMBER: HCC8W80D010MW-HM86080827-81WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	451.1	6.8
10°-20°	1247.1	18.8
20°-30°	1847.7	27.9
30°-40°	1707.3	25.8
40°-50°	787.2	11.9
50°-60°	414.0	6.2
60°-70°	146.3	2.2
70°-80°	22.9	0.3
80°-90°	2.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3545.9	53.5
0°-40°	5253.2	79.3
0°-60°	6454.4	97.4
0°-90°	6625.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6625.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4919	
5°	4790	451
15°	4411	1247
25°	4040	1848
35°	2874	1707
45°	966	787
55°	454	414
65°	142	146
75°	17	23
85°	0	2
90°	0	



TEST NUMBER: P585198

CATALOG NUMBER: HCC8W80D010MW-HM86080827-81WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4919.4
2.5°	4877.8
5°	4790.2
7.5°	4694.4
10°	4590.3
12.5°	4490.4
15°	4411.2
17.5°	4340.3
20°	4252.9
22.5°	4157.1
25°	4040.5
27.5°	3882.2
30°	3657.2
32.5°	3336.5
35°	2874.2
37.5°	2207.6
40°	1582.9
42.5°	1187.1
45°	966.4
47.5°	820.5
50°	691.4
52.5°	566.4
55°	454.1
57.5°	358.2
60°	274.9
62.5°	208.3
65°	141.6
67.5°	83.3
70°	49.9
72.5°	29.1
75°	16.6
77.5°	12.5
80°	8.3
82.5°	4.2
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)