

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585199

Luminaire Tested: **HCC8S80D010SL-HM86080827-81WDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585199
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S80D010SL-HM86080827-81WDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6396.9 lumens
Efficiency: N/A
Efficacy: 91.4 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 70
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585199
CATALOG NUMBER: HCC8S80D010SL-HM86080827-81WDW

Luminous Intensity Polar Plot





TEST NUMBER: P585199

CATALOG NUMBER: HCC8S80D010SL-HM86080827-81WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	127891
5°	127732
10°	126469
15°	124957
20°	123799
25°	122409
30°	115497
35°	94050
40°	51964
45°	34682
50°	30760
55°	28881
60°	28505
65°	28259
70°	25524
75°	22816
80°	19978
85°	17655



TEST NUMBER: P585199

CATALOG NUMBER: HCC8S80D010SL-HM86080827-81WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	391.1	6.1
10°-20°	1105.2	17.3
20°-30°	1642.2	25.7
30°-40°	1478.9	23.1
40°-50°	655.6	10.2
50°-60°	485.6	7.6
60°-70°	377.6	5.9
70°-80°	204.7	3.2
80°-90°	56.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3138.5	49.1
0°-40°	4617.4	72.2
0°-60°	5758.6	90.0
0°-90°	6396.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6396.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4147	
5°	4126	391
15°	3914	1105
25°	3598	1642
35°	2498	1479
45°	795	656
55°	537	486
65°	387	378
75°	192	205
85°	50	56
90°	0	



TEST NUMBER: P585199

CATALOG NUMBER: HCC8S80D010SL-HM86080827-81WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4147.4
2.5°	4139.0
5°	4126.5
7.5°	4093.3
10°	4039.0
12.5°	3976.6
15°	3914.2
17.5°	3851.6
20°	3772.6
22.5°	3693.5
25°	3597.7
27.5°	3451.9
30°	3243.7
32.5°	2944.0
35°	2498.4
37.5°	1865.4
40°	1290.9
42.5°	953.6
45°	795.3
47.5°	703.8
50°	641.2
52.5°	583.0
55°	537.2
57.5°	499.7
60°	462.2
62.5°	428.9
65°	387.3
67.5°	337.3
70°	283.1
72.5°	237.3
75°	191.5
77.5°	149.9
80°	112.5
82.5°	79.1
85°	49.9
87.5°	20.8
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)