

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585200

Luminaire Tested: **HCC8W80D010BZ-HM86080827-81WDWB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585200  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W80D010BZ-HM86080827-81WDWB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6859.2 lumens  
Efficiency: N/A  
Efficacy: 98.0 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 70  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585200  
CATALOG NUMBER: HCC8W80D010BZ-HM86080827-81WDWB

### Luminous Intensity Polar Plot





TEST NUMBER: P585200  
 CATALOG NUMBER: HCC8W80D010BZ-HM86080827-81WDWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90																			
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81																			
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73																			
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65																			
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59																			
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54																			
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51	49																			
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45																			
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	47	43	41																			
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	120465
5°	119638
10°	119321
15°	122451
20°	132571
25°	142129
30°	138952
35°	115703
40°	71084
45°	49217
50°	37563
55°	24628
60°	15412
65°	11550
70°	11640
75°	13404
80°	14792
85°	13268



TEST NUMBER: P585200  
 CATALOG NUMBER: HCC8W80D010BZ-HM86080827-81WDWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	367.2	5.4
10°-20°	1101.1	16.1
20°-30°	1895.6	27.6
30°-40°	1836.5	26.8
40°-50°	904.6	13.2
50°-60°	426.9	6.2
60°-70°	168.2	2.5
70°-80°	116.1	1.7
80°-90°	43.0	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3363.9	49.0
0°-40°	5200.4	75.8
0°-60°	6531.9	95.2
0°-90°	6859.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6859.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3907	
5°	3865	367
15°	3836	1101
25°	4177	1896
35°	3074	1837
45°	1129	905
55°	458	427
65°	158	168
75°	112	116
85°	38	43
90°	0	

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



TEST NUMBER: P585200

CATALOG NUMBER: HCC8W80D010BZ-HM86080827-81WDWB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3906.6
2.5°	3894.1
5°	3865.0
7.5°	3835.7
10°	3810.7
12.5°	3806.6
15°	3835.7
17.5°	3923.2
20°	4039.9
22.5°	4144.0
25°	4177.3
27.5°	4102.3
30°	3902.4
32.5°	3573.4
35°	3073.6
37.5°	2386.4
40°	1765.9
42.5°	1370.2
45°	1128.6
47.5°	949.5
50°	783.0
52.5°	616.4
55°	458.1
57.5°	333.2
60°	249.9
62.5°	195.7
65°	158.3
67.5°	137.4
70°	129.1
72.5°	120.8
75°	112.5
77.5°	100.0
80°	83.3
82.5°	62.4
85°	37.5
87.5°	16.6
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)