

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585213

Luminaire Tested: **HCC8W80D010MW-HM86080830-81WDBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585213
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W80D010MW-HM86080830-81WDBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6193.6 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 70
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585213
CATALOG NUMBER: HCC8W80D010MW-HM86080830-81WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P585213
 CATALOG NUMBER: HCC8W80D010MW-HM86080830-81WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92				
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83				
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75				
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68				
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62				
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56				
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51				
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47				
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43				
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	116043
5°	115081
10°	113562
15°	114857
20°	124032
25°	135637
30°	133995
35°	111148
40°	65421
45°	42741
50°	33130
55°	22010
60°	10713
65°	3320
70°	1118
75°	989
80°	746
85°	1486



TEST NUMBER: P585213
 CATALOG NUMBER: HCC8W80D010MW-HM86080830-81WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	352.1	5.7
10°-20°	1033.6	16.7
20°-30°	1807.2	29.2
30°-40°	1757.9	28.4
40°-50°	799.5	12.9
50°-60°	370.7	6.0
60°-70°	62.1	1.0
70°-80°	7.7	0.1
80°-90°	2.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3192.9	51.6
0°-40°	4950.8	79.9
0°-60°	6120.9	98.8
0°-90°	6193.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6193.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3763	
5°	3718	352
15°	3598	1034
25°	3986	1807
35°	2953	1758
45°	980	799
55°	409	371
65°	46	62
75°	8	8
85°	4	3
90°	0	



TEST NUMBER: P585213
CATALOG NUMBER: HCC8W80D010MW-HM86080830-81WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	3763.2
2.5°	3755.0
5°	3717.8
7.5°	3676.4
10°	3626.8
12.5°	3589.5
15°	3597.8
17.5°	3664.0
20°	3779.7
22.5°	3912.0
25°	3986.5
27.5°	3945.2
30°	3763.2
32.5°	3444.8
35°	2952.6
37.5°	2274.4
40°	1625.2
42.5°	1211.7
45°	980.1
47.5°	827.1
50°	690.6
52.5°	550.0
55°	409.4
57.5°	281.2
60°	173.7
62.5°	95.1
65°	45.5
67.5°	20.7
70°	12.4
72.5°	8.3
75°	8.3
77.5°	4.2
80°	4.2
82.5°	4.2
85°	4.2
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)