

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593898

Luminaire Tested: **HCC8W80D010SL-HM86080850-81MDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593898
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W80D010SL-HM86080850-81MDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7712.5 lumens
Efficiency: N/A
Efficacy: 110.2 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.95
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 70
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593898
CATALOG NUMBER: HCC8W80D010SL-HM86080850-81MDW

Luminous Intensity Polar Plot





TEST NUMBER: P593898
 CATALOG NUMBER: HCC8W80D010SL-HM86080850-81MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		94	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	98	89	83	78	95	88	82	78	85	80	76		83	78	75		80	77	74	72
4	91	82	75	70	89	81	74	69	78	73	69		76	72	68		74	70	67	65
5	86	76	68	63	84	75	68	63	73	67	62		71	66	62		69	65	61	59
6	81	70	63	58	79	69	62	57	67	61	57		66	61	56		64	60	56	54
7	76	65	58	53	74	64	57	53	63	57	52		62	56	52		60	55	52	50
8	72	61	54	49	70	60	53	49	59	53	48		58	52	48		57	52	48	46
9	68	57	50	45	67	56	50	45	55	49	45		54	49	45		53	48	45	43
10	64	53	46	42	63	53	46	42	52	46	42		51	46	42		50	45	42	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	197211
5°	191835
10°	180520
15°	170912
20°	164408
25°	158056
30°	140376
35°	89397
40°	49895
45°	41786
50°	37726
55°	35558
60°	32440
65°	29259
70°	25822
75°	22959
80°	20351
85°	18433



TEST NUMBER: P593898
 CATALOG NUMBER: HCC8W80D010SL-HM86080850-81MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	577.8	7.5
10°-20°	1509.9	19.6
20°-30°	2106.4	27.3
30°-40°	1515.7	19.7
40°-50°	751.1	9.7
50°-60°	587.7	7.6
60°-70°	397.8	5.2
70°-80°	206.6	2.7
80°-90°	59.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4194.0	54.4
0°-40°	5709.7	74.0
0°-60°	7048.5	91.4
0°-90°	7712.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7712.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6395	
5°	6197	578
15°	5354	1510
25°	4645	2106
35°	2375	1516
45°	958	751
55°	661	588
65°	401	398
75°	193	207
85°	52	60
90°	0	



TEST NUMBER: P593898
CATALOG NUMBER: HCC8W80D010SL-HM86080850-81MDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	6395.4
2.5°	6338.1
5°	6197.4
7.5°	5999.6
10°	5765.2
12.5°	5546.4
15°	5353.7
17.5°	5171.4
20°	5010.1
22.5°	4848.6
25°	4645.4
27.5°	4353.9
30°	3942.4
32.5°	3296.6
35°	2374.8
37.5°	1619.7
40°	1239.5
42.5°	1067.6
45°	958.2
47.5°	864.5
50°	786.4
52.5°	718.8
55°	661.4
57.5°	593.7
60°	526.0
62.5°	458.2
65°	401.0
67.5°	343.7
70°	286.4
72.5°	239.6
75°	192.7
77.5°	151.0
80°	114.6
82.5°	83.3
85°	52.1
87.5°	26.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)