

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585267

Luminaire Tested: **HCC8W80D010MB-HM86080927-81WDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585267
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W80D010MB-HM86080927-81WDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5571.7 lumens
Efficiency: N/A
Efficacy: 79.6 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 70
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585267
CATALOG NUMBER: HCC8W80D010MB-HM86080927-81WDW

Luminous Intensity Polar Plot





TEST NUMBER: P585267

CATALOG NUMBER: HCC8W80D010MB-HM86080927-81WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	111387
5°	111252
10°	110153
15°	108832
20°	107825
25°	106615
30°	100596
35°	81914
40°	45258
45°	30208
50°	26793
55°	25155
60°	24829
65°	24611
70°	22233
75°	19873
80°	17403
85°	15391



TEST NUMBER: P585267
 CATALOG NUMBER: HCC8W80D010MB-HM86080927-81WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	340.6	6.1
10°-20°	962.6	17.3
20°-30°	1430.3	25.7
30°-40°	1288.1	23.1
40°-50°	571.0	10.2
50°-60°	422.9	7.6
60°-70°	328.9	5.9
70°-80°	178.3	3.2
80°-90°	48.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2733.5	49.1
0°-40°	4021.6	72.2
0°-60°	5015.6	90.0
0°-90°	5571.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5571.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3612	
5°	3594	341
15°	3409	963
25°	3134	1430
35°	2176	1288
45°	693	571
55°	468	423
65°	337	329
75°	167	178
85°	44	49
90°	0	



TEST NUMBER: P585267
CATALOG NUMBER: HCC8W80D010MB-HM86080927-81WDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3612.2
2.5°	3604.9
5°	3594.1
7.5°	3565.1
10°	3517.9
12.5°	3463.6
15°	3409.1
17.5°	3354.8
20°	3285.8
22.5°	3217.0
25°	3133.5
27.5°	3006.5
30°	2825.2
32.5°	2564.1
35°	2176.0
37.5°	1624.8
40°	1124.3
42.5°	830.5
45°	692.7
47.5°	612.9
50°	558.5
52.5°	507.7
55°	467.9
57.5°	435.2
60°	402.6
62.5°	373.6
65°	337.3
67.5°	293.8
70°	246.6
72.5°	206.8
75°	166.8
77.5°	130.6
80°	98.0
82.5°	69.0
85°	43.5
87.5°	18.2
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)