

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585284

Luminaire Tested: **HCC8W80D010BZ-HM86080930-81WDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585284
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W80D010BZ-HM86080930-81WDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5960.5 lumens
Efficiency: N/A
Efficacy: 85.2 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 70
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585284
CATALOG NUMBER: HCC8W80D010BZ-HM86080930-81WDW

Luminous Intensity Polar Plot





TEST NUMBER: P585284

CATALOG NUMBER: HCC8W80D010BZ-HM86080930-81WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	119164
5°	119019
10°	117843
15°	116430
20°	115352
25°	114059
30°	107618
35°	87632
40°	48417
45°	32319
50°	28664
55°	26908
60°	26562
65°	26333
70°	23784
75°	21267
80°	18610
85°	16487



TEST NUMBER: P585284
 CATALOG NUMBER: HCC8W80D010BZ-HM86080930-81WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	364.4	6.1
10°-20°	1029.8	17.3
20°-30°	1530.2	25.7
30°-40°	1378.0	23.1
40°-50°	610.9	10.2
50°-60°	452.4	7.6
60°-70°	351.8	5.9
70°-80°	190.8	3.2
80°-90°	52.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2924.4	49.1
0°-40°	4302.3	72.2
0°-60°	5365.7	90.0
0°-90°	5960.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5960.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3864	
5°	3845	364
15°	3647	1030
25°	3352	1530
35°	2328	1378
45°	741	611
55°	500	452
65°	361	352
75°	178	191
85°	47	52
90°	0	



TEST NUMBER: P585284
CATALOG NUMBER: HCC8W80D010BZ-HM86080930-81WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3864.4
2.5°	3856.6
5°	3845.0
7.5°	3814.0
10°	3763.5
12.5°	3705.3
15°	3647.1
17.5°	3588.9
20°	3515.2
22.5°	3441.4
25°	3352.3
27.5°	3216.5
30°	3022.4
32.5°	2743.0
35°	2327.9
37.5°	1738.2
40°	1202.8
42.5°	888.5
45°	741.1
47.5°	655.7
50°	597.5
52.5°	543.1
55°	500.5
57.5°	465.6
60°	430.7
62.5°	399.6
65°	360.9
67.5°	314.3
70°	263.8
72.5°	221.2
75°	178.5
77.5°	139.7
80°	104.8
82.5°	73.7
85°	46.6
87.5°	19.4
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)