

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585277

Luminaire Tested: **HCC8W80D010MW-HM86080930-81NDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585277
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W80D010MW-HM86080930-81NDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5196.0 lumens
Efficiency: N/A
Efficacy: 74.2 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.92
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 70
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585277
CATALOG NUMBER: HCC8W80D010MW-HM86080930-81NDW

Luminous Intensity Polar Plot





TEST NUMBER: P585277
 CATALOG NUMBER: HCC8W80D010MW-HM86080930-81NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90
2	105	99	94	90	102	97	92	88	94	90	87	91	87	85	88	85	83	81
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	72	68	67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	76	66	59	54	64	58	54	63	58	54	62	57	53	52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48
9	69	58	51	47	68	57	51	47	56	51	46	55	50	46	55	50	46	45
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	129513
5°	129168
10°	127014
15°	125162
20°	122158
25°	115958
30°	95647
35°	49242
40°	32972
45°	28267
50°	24394
55°	21284
60°	18909
65°	16994
70°	15390
75°	13868
80°	12413
85°	12383



TEST NUMBER: P585277
 CATALOG NUMBER: HCC8W80D010MW-HM86080930-81NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	394.5	7.6
10°-20°	1103.0	21.2
20°-30°	1528.3	29.4
30°-40°	918.0	17.7
40°-50°	502.5	9.7
50°-60°	357.0	6.9
60°-70°	231.8	4.5
70°-80°	123.8	2.4
80°-90°	37.0	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3025.9	58.2
0°-40°	3943.9	75.9
0°-60°	4803.4	92.4
0°-90°	5196.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5196.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4200	
5°	4173	395
15°	3921	1103
25°	3408	1528
35°	1308	918
45°	648	503
55°	396	357
65°	233	232
75°	116	124
85°	35	37
90°	0	



TEST NUMBER: P585277

CATALOG NUMBER: HCC8W80D010MW-HM86080930-81NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4200.0
2.5°	4192.3
5°	4172.9
7.5°	4126.3
10°	4056.4
12.5°	3990.4
15°	3920.6
17.5°	3831.3
20°	3722.6
22.5°	3590.7
25°	3408.1
27.5°	3120.9
30°	2686.2
32.5°	1968.0
35°	1308.1
37.5°	966.5
40°	819.1
42.5°	725.9
45°	648.2
47.5°	574.5
50°	508.5
52.5°	446.4
55°	395.9
57.5°	349.3
60°	306.6
62.5°	267.9
65°	232.9
67.5°	198.0
70°	170.7
72.5°	139.7
75°	116.4
77.5°	93.2
80°	69.9
82.5°	50.4
85°	35.0
87.5°	15.6
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)