

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585315

Luminaire Tested: **HCC8W80D010SL-HM86080940-81WDBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585315
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W80D010SL-HM86080940-81WDBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6817.7 lumens
Efficiency: N/A
Efficacy: 97.4 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 70
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585315
CATALOG NUMBER: HCC8W80D010SL-HM86080940-81WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P585315

CATALOG NUMBER: HCC8W80D010SL-HM86080940-81WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62			
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	127739
5°	126677
10°	125007
15°	126432
20°	136535
25°	149311
30°	147501
35°	122355
40°	72014
45°	47050
50°	36469
55°	24225
60°	11792
65°	3656
70°	1235
75°	1096
80°	799
85°	1592



TEST NUMBER: P585315
 CATALOG NUMBER: HCC8W80D010SL-HM86080940-81WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	387.6	5.7
10°-20°	1137.8	16.7
20°-30°	1989.3	29.2
30°-40°	1935.1	28.4
40°-50°	880.0	12.9
50°-60°	408.0	6.0
60°-70°	68.4	1.0
70°-80°	8.4	0.1
80°-90°	3.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3514.7	51.6
0°-40°	5449.8	79.9
0°-60°	6737.8	98.8
0°-90°	6817.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6817.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4142	
5°	4092	388
15°	3960	1138
25°	4388	1989
35°	3250	1935
45°	1079	880
55°	451	408
65°	50	68
75°	9	8
85°	4	3
90°	0	



TEST NUMBER: P585315
CATALOG NUMBER: HCC8W80D010SL-HM86080940-81WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	4142.5
2.5°	4133.4
5°	4092.4
7.5°	4046.9
10°	3992.3
12.5°	3951.3
15°	3960.4
17.5°	4033.2
20°	4160.7
22.5°	4306.3
25°	4388.4
27.5°	4342.8
30°	4142.5
32.5°	3792.0
35°	3250.3
37.5°	2503.7
40°	1789.0
42.5°	1333.8
45°	1078.9
47.5°	910.4
50°	760.2
52.5°	605.4
55°	450.6
57.5°	309.5
60°	191.2
62.5°	104.8
65°	50.1
67.5°	22.7
70°	13.7
72.5°	9.2
75°	9.2
77.5°	4.5
80°	4.5
82.5°	4.5
85°	4.5
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)