

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P886464

Luminaire Tested: ML204LSFLD2W1E-TIR1D40FL-TL2RDMB-400LM-3500K

Issue Date: 6/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P886464
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-79)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 6/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML204LSFLD2W1E-TIR1D40FL-TL2RDMB-400LM-3500K
Description: 2IN ROUND ML FLEX, SELECTABLE CCT, WITH 40D TIR, MATTE BLACK TRIM
Light Source: (1) D2W LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 406.7 lumens
Efficiency: N/A
Efficacy: 65.6 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.67
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 6.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P886464

CATALOG NUMBER: ML204LSFLD2W1E-TIR1D40FL-TL2RDMB-400LM-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P886464

CATALOG NUMBER: ML204LSFLD2W1E-TIR1D40FL-TL2RDDB-400LM-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66
9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63
10	79	70	65	62	78	70	65	62	69	65	62	68	64	62	68	64	61	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	381629
5°	373776
10°	341926
15°	285886
20°	218786
25°	146657
30°	90526
35°	43065
40°	19064
45°	6070
50°	1689
55°	602
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6070 cd/sqm



TEST NUMBER: P886464

CATALOG NUMBER: ML204LSFLD2W1E-TIR1D40FL-TL2RDMB-400LM-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.7	17.1
10°-20°	153.9	37.8
20°-30°	124.6	30.6
30°-40°	49.1	12.1
40°-50°	8.7	2.1
50°-60°	0.7	0.2
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	348.2	85.6
0°-40°	397.4	97.7
0°-60°	406.7	100.0
0°-90°	406.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	406.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	774	
5°	755	70
15°	560	154
25°	269	125
35°	72	49
45°	9	9
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P886464

CATALOG NUMBER: ML204LSFLD2W1E-TIR1D40FL-TL2RDMB-400LM-3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	773.5
2.5°	771.3
5°	754.7
7.5°	725.1
10°	682.5
12.5°	626.9
15°	559.7
17.5°	489.7
20°	416.7
22.5°	341.6
25°	269.4
27.5°	208.7
30°	158.9
32.5°	111.9
35°	71.5
37.5°	45.5
40°	29.6
42.5°	18.1
45°	8.7
47.5°	3.6
50°	2.2
52.5°	1.4
55°	0.7
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)